



TECHNICAL INFORMATION

| | |
|------------------------|----------------------|
| Input Power: | AC:200-240V, 50/60Hz |
| Body Type: | Iron |
| Operation Temperature: | -20°C to +40°C |
| Dimmable: | No |
| Dimension: | 615x45x50mm |

SINGLE BATTEN FITTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 6052 -

[View more details](#)

TUBE-BATTEN FITTING 60CMx1 Tubes

Compatible with any
60cm LED tubes.

*LED tubes are not included.



FEATURES

- Robust Batten Fixtures that are compatible with T8 LED Tubes
- ABS Holders for better endurance
- Sturdy and durable Iron build
- Easy to install and requires little maintenance
- No ballast or starter required
- Suitable for residential, warehouses, workshops, utilities etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 0.36
Unit CBM: 0.00122
Dimension: 615x45x50mm

MASTER BOX PACKAGING

Box Qty: 20
Length (Box) mm: 616
Width (Box) mm: 36
Height (Box) mm: 52

LISTING DETAILS

Commodity Code: 9405109890
EanCode: 3800230624642