



TECHNICAL INFORMATION

Input Power:	AC:200-240V, 50/60Hz
Body Type:	Iron
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Dimension:	1225x55x50mm

DOUBLE BATTEN

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 6055 -

[View more details](#)

TUBE-BATTEN FITTING 120CMx2 Tubes

Compatible with any
120cm LED tubes.

*LED tubes are not included.



FEATURES

- Robust Batten Fixtures that are compatible with T8 LED Tubes
- ABS Holders for better endurance
- Sturdy and durable Iron build
- Easy to install and requires little maintenance
- No ballast or starter required
- Suitable for residential, warehouses, workshops, utilities etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs):	0.75
Unit CBM:	0.00021
Dimension:	1225x55x50mm

MASTER BOX PACKAGING

Box Qty:	12
Length (Box) mm:	1230
Width (Box) mm:	55
Height (Box) mm:	35

LISTING DETAILS

Commodity Code:	9405109890
EanCode:	3800230624673