



TECHNICAL INFORMATION

Watts:	36
Lumens:	2880
Input Power:	AC:220-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Plastic + ABS
PF:	>0.9
LED Chip Type:	SMD
CRI:	>70
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	120°
Color:	6400K
Dimension:	1200x76x66mm
Ambient Light:	50 Max
Battery Type:	Ni-Cd 9.6V, 2200mAh



IP65
RATING



2 YEAR
WARRANTY

FEATURES

- Using high power SMD technology which makes it more reliable and durable
- 3 Hours Emergency operation time
- Complete protection from water, dust and corrosion - IP65 Rated
- Designed for maximum efficiency & minimal glare
- Save up to 80% in electricity consumption compared to a fluorescent lighting fixture
- Long Lifespan, Low maintenance and energy saving
- Suitable for parking lots, warehouses, garages, storage docks, workshops etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warrant

CE/EMC

CE/LVD




EMERGENCY WATERPROOF

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 6449 - 1406 940

[View more details](#)



PACKAGING

Gross Weight (Kgs): 1.9
Unit CBM: 0.006944
Dimension: 1200x76x66mm

MASTER BOX PACKAGING

Box Qty: 12
Qty Per Pallet: 180
Length (Box) mm: 70
Width (Box) mm: 80
Height (Box) mm: 1240

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157632133