



TECHNICAL INFORMATION

Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Body Type:	Aluminium
Operation Temperature:	-25°C to +50°C
Dimension:	95x95x335mm

GARDEN SPIKES FITTINGS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 7517 - 938

[View more details](#)

GARDEN SPIKE



GU10

Compatible with any standard **GU10** lamp.

**EASY
INSTALLATION**

BLACK FINISH



FEATURES

- Garden spike fitting designed for easy installation
- Strong and sturdy Aluminium body
- Ingress protection IP44
- Compatible with GU10 holder type (Fitting only - light not included)
- Easy to install and requires little maintenance
- Suitable for pathways, driveways, tree uplighting etc.

CE/EMC CE/LVD



PACKAGING

Gross Weight (Kgs):	0.525
Unit CBM:	0.00228
Dimension:	95x95x335mm

MASTER BOX PACKAGING

Box Qty:	12
Qty Per Pallet:	480

LISTING DETAILS

Commodity Code:	9405109890
EanCode:	3800157617765