



### TECHNICAL INFORMATION

Wireless Frequency:	2.4G WIFI
Plug Type:	BS Plug
Input Power:	AC:90-250V, 50/60Hz
Input Current:	13A
Unit Color:	White
Body Type:	PC
Dimension:	146x86x32mm
Rated Load:	Max 2900W
USB Output:	5V/2.1A
On/Off Cycles:	>10000



### FEATURES

- Wi-Fi enabled Wall Socket with two USB ports
- Sturdy PC design
- Wireless frequency: 2.4GHz
- Compatible with Amazon Alexa and Google Home
- Easy to install and requires little maintenance
- Two USB ports with output of 5V - 2.1A
- Can be controlled via V-TAC Smart Home app or Alexa and Google Home

### WALL SOCKETS

WiFi-supported home solutions to convert any device into a smart device, and ultimately convert any home into a smart home. Have a systematic, unified control on all your smart devices through the official V-TAC app, Amazon Alexa, and Google Home.

*One brand, endless solutions..testing*

SKU: 8446 - 940

[View more details](#)

### WIFI WALL SOCKET 3 Step Processing

**Step.1**  
Install the device & Register an account with QR Code

**Step.2**  
Pair the device with V-TAC Smart Home app

**Step.3**  
Link the device to Amazon Alexa or Google Home

### PACKAGING

Gross Weight (Kgs): 0.244  
Unit CBM: 0.000625  
Dimension: 146x86x32mm

### MASTER BOX PACKAGING

Box Qty: 100  
Length (Box) mm: 160  
Width (Box) mm: 34  
Height (Box) mm: 91

### LISTING DETAILS

EanCode: 3800157644648