

# 21.5" LED Monitor 1920x1080 New Model: M2286



## Features:

- 170° / 160° Viewing angle
- Low power consumption
- CE/FCC Certificated
- Hard Glass Feasible
- Blue light technology

## Accessories

- VGA Cable
- Audio Cable
- Power Cable
- Manual

## Specifications

Panel	
Size	21.5" LED-Backlit
Resolution	1920x1080
Color Support	16.7M
Brightness	250cd/m <sup>2</sup>
Contrast Ratio	1000:1
Response Time	5ms
Speaker	2x2w
I/O	
VGA IN	x1
DVI IN	x1
HDMI IN	x1 (optional)
Audio IN	x1
Power	
Consumption	<35W(on),0.5W(off)
Power Supply	Internal
Voltage	100-240V AC,60/50Hz
Operating Condition	
Temperature	0°C - 40°C
Humidity	10%-80%
Others	
VESA	100x100mm
Box Dimension (L*W*H)	563x111x406mm
Loading Quantity (With Pallets)	20GP:800 pcs
	40GP:1680 pcs
	40HQ:1848 pcs
Gross Weight	3.9Kgs
MOQ	500 pcs
Approvals	CE / FCC