

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1707220008](#)
Status: **Active**
Description: 10GBE 2x8 STACKED-(P/F) No CMS-LP

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-170849-0001-000 \(PDF\)](#)
[Application Specification AS-170711-0002-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E107635

General

Product Family Modular Jacks/Plugs
Series [170722](#)
UPC 884982738287

Physical

Flammability 94V-0
Net Weight 158.205/g

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification AS-170711-0002-001
Packaging Specification PK-170849-0001-000
S-Parameter Model SP-170423-1339

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 7(c)-I

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[170722](#) Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
10 Gigabit Ethernet 2-by-3 Magnetic Jack Assemblies with Press-fit Tails.	622024430
1 Gigabit Ethernet and 10 Gigabit Ethernet 2 by 8 Magnetic Jack Removal Tool	622030550