

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1060520040](#)
Status: **Active**
Overview: [LC Connectors, Adapters and Cable Assemblies](#)
Description: LC Loopback, Multimode, 62.5/125µm fiber

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|--|
| Product Family | Fiber Optic Assemblies |
| Series | 106052 |
| Boot Type | N/A |
| Comments | One Piece |
| Connector to Connector | LC-to-LC |
| Mode | Multimode |
| Overview | LC Connectors, Adapters and Cable Assemblies |
| Product Name | LC |
| UPC | 822350267175 |

Physical

| | |
|-----------------------|------------|
| Cable Length | LOOPBACK |
| Cable Size | 250µm |
| Fiber (Core/Cladding) | 62.5/125µm |
| Net Weight | 2.422/g |
| Single Ended | No |
| Wire/Cable Type | Simplex |

Solder Process Data


| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

| | |
|--------------------|-----------|
| Engineering Number | 860520040 |
|--------------------|-----------|

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | SD-106052-0040 |
|---------------|----------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[106052](#) Series