


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **5031751210**
Status: **Active**
Overview: CLIK-Mate Wire-to-Board Connectors
Description: 1.50mm Pitch, CLIK-Mate PCB Receptacle, Single Row, Through Hole, Right-Angle, Tin Plating, Positive Lock, without Peg, 12 Circuits, Natural

Documents:

| | |
|---|---|
| 3D Model | Product Specification 5025781002-PS-000 (PDF) |
| Drawing (PDF) | Application Specification AS-502578-001-001 (PDF) |
| 3D Model (PDF) | Packaging Specification SPK-503175-001-001 (PDF) |
| Product Specification 5025780002-PS-000 (PDF) | RoHS Certificate of Compliance (PDF) |



General

| | |
|----------------|--|
| Product Family | PCB Receptacles |
| Series | 503175 |
| Application | Signal, Wire-to-Board |
| Overview | CLIK-Mate Wire-to-Board Connectors |
| Product Name | CLIK-Mate |
| UPC | 883906059613 |

Physical

| | |
|--------------------------------|----------------|
| Circuits (Loaded) | 12 |
| Circuits (maximum) | 12 |
| Color - Resin | Beige |
| Durability (mating cycles max) | 30 |
| Glow-Wire Capable | No |
| Guide to Mating Part | Yes |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 1014.001/mg |
| Number of Rows | 1 |
| Orientation | Right Angle |
| PCB Locator | No |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.60mm, 2.40mm |
| Packaging Type | Tray |
| Pitch - Mating Interface | 1.50mm |
| Pitch - Termination Interface | 1.50mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 2.0A |
| Voltage - Maximum | 100V |

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|--------------------------------------|
| Application Specification | AS-502578-001-001 |
| Packaging Specification | SPK-503175-001-001 |
| Product Specification | 5025780002-PS-000, 5025781002-PS-000 |
| Sales Drawing | 5031750000-SD-000 |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[503175 Series](#)

Mates With

[502578 Crimp Housing](#) . [502579 Crimp Terminal](#)

This document was generated on 08/10/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION