

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348050111](#)
Status: **Active**
Overview: [CTX Crimp Terminals](#)
Description: CTX150 Female Terminal, Tin (Sn), 22 AWG D-Wind, Left Payoff, Grip Code S

Documents:

[Drawing \(PDF\)](#) [Packaging Specification 313025040-000 \(PDF\)](#)
[Product Specification PS-502307-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-502307-001-001 \(PDF\)](#)

General

Product Family Crimp Terminals
Series [34805](#)
Application Power, Wire-to-Wire
Crimp Quality Equipment Yes
Overview [CTX Crimp Terminals](#)
Product Name CTX150
UPC 884982651166

Physical

Durability (mating cycles max) 10
Gender Female
Material - Metal Copper Alloy
Material - Plating Mating Tin
Material - Plating Termination Nickel
Net Weight 0.224/g
Packaging Type Reel
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 2.80mm
Wire Size AWG 22
Wire Size mm² 0.35-0.50

Electrical

Current - Maximum per Contact 15.0A
Voltage - Maximum 250V


Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification [AS-502307-001-001](#)
Packaging Specification [313025040-000](#)
Product Specification [PS-502307-001-001](#)
Sales Drawing [SD-34805-001-001](#)



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34805 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for CTX 1.50mm Receptacle Terminal, 0.30, 0.35, and 0.50mm ² Wires	638193900
FineAdjust Applicator for CTX150 Receptacle Terminals, 0.30mm ² , 0.35mm ² , & 0.50mm ²	639010400

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION