

## Product information

# 35 41 115

## Electronics Pliers

DIN ISO 9655



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- Load-optimised for a more direct feel when working
- For gripping, holding and bending
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Soft transitions; no sharp edges
- Low-friction double spring for gentle and even opening
- The polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Narrow sleeves pulled up to the head of the pliers enable the tool to be guided securely and comfortably, also between thumb and index finger
- Ball bearing chrome steel

### General

Article No.	35 41 115
EAN	4003773082248
Head	mirror polished
Handles	with multi-component grips
weight	61 g
Dimensions	115 x 66 x 14 mm
Standard	DIN ISO 9655

### Technische Attribute

	22.5 mm
	6.5 mm
	2.0 mm
	1.0 mm
Head width	11.0 mm
Dimensions angle	45

### Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

*technical change and errors excepted*

