

## Product information

# 48 31 J1

## Precision Circlip Pliers

For internal circlips in bore holes

With overstretching limiter

DIN 5256 C



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- With overexpansion guard (adjustable using end stop)
- Adjustment using hexagonal screw
- Ideal for series production as excessive expansion of rings is effectively prevented
- DIN 5256 C, straight tips
- With overstretching limiter for standardized assembly in accordance with DIN 472
- The adjustable stop screw prevents the rings from overstretching
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened

### General

Article No.	48 31 J1
EAN	4003773073864
Pliers	grey atramentized
Handles	with non-slip plastic coating
weight	105 g
Dimensions	140 x 48 x 12 mm
Standard	DIN 5256 C

### Technische Attribute

Style	3
Size of bore	Ø 12 – 25 mm
Tips (diameter)	Ø 1.3 mm

### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

*technical change and errors excepted*