

Product information

98 37 9/16"

- For imperial hexagonal head screws
- Basic tool chrome plated
- With double-hex
- Chrome Vanadium steel

12-Point Socket

With internal square 3/8"

IEC 60900 DIN EN 60900



⚠ 1000 V 

General

Article No.	98 37 9/16"
EAN	4003773020721
weight	39 g
Dimensions	47 x 23 x 33 mm
Standard	DIN EN 60900 IEC 60900

Technische Attribute

dia. of effective tool side d max.	23.7 mm
------------------------------------	---------

Classification

eCl@ss 5.1.4	21040219
proficl@ss 6.0	AAA805c006

technical change and errors excepted