




## SEB 2620 F6,3 rot/red

Measuring and Testing Equipment:Sockets:4 mm safety system

### Product description

Description	Safety built-in socket, 4 mm diameter, contact-protected, with 6.3 x 0.8 tab connector complying with DIN 46 244, gold-plated brass. For installation into switchpanels and equipment chassis with wall thicknesses up to 6 mm. Accessory BES 1000. Installation hole: 12,2 mm diameter. Tightening torque: 50 Ncm.
Type	SEB 2620 F6,3 rot/red
Order No.	972 356-101
System	4 mm safety system
Housing Color	red
Other standard types	black color, order no. 972 356-100; blue color, order no. 972 356-102; yellow color, order no. 972 356-103; green color, order no. 972 356-104; yellow/green color, order no. 972 356-188

### Drawing



### Technical data

Type of contact	socket
Type of termination	flat plug 6.3 x 0.8
Standard	IEC 61010
Rated voltage	AC/DC 1000 V

Measurement Category	CAT II
Rated current	32 A
Contact resistance	5 mOhm
Mounting	screw
<b>Material</b>	
Contact material	brass
Contact surface material	gold-plated
Housing material	PA
<b>Environmental conditions</b>	
Temperature range	-40 °C to +80 °C
<b>Inflammability class</b>	
Housing	94 V-2