

Blue flash



Standard length

Order code	Cutting diameter (mm)	Cutting diameter (in)	Price each
144-0483	4.5	3/16	
144-0484	5	-	
144-0485	5.5	7/32	
144-0486	6	-	
144-0487	6.5	1/4	
144-0488	7	9/32	
144-0489	8	5/16	
144-0490	10	-	

150mm overall length

Order code	Cutting diameter (mm)	Cutting diameter (in)	Price each
144-0448	4.5	3/16	
144-0449	5	-	
144-0450	5.5	7/32	
144-0451	6	-	
144-0452	6.5	1/4	
144-0453	7	9/32	
144-0454	8	5/16	
144-0455	10	-	
144-0456	12	15/32	
144-0458	13	1/2	

220mm overall length

Order code	Cutting diameter (mm)	Cutting diameter (in)	Price each
No Order Code	6	-	
No Order Code	8	5/16	
No Order Code	12	15/32	