

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2153411101](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead Mini-Fit Jr. Female-to-Pigtail, Tin (Sn) Plating, 75.00mm Length, 20 AWG, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Datasheet \(PDF\)](#)

**General**

Product Family Cable Assemblies  
 Series [215341](#)  
 Application Power, Wire-to-Board, Wire-to-Wire  
 Assembly Configuration Pre-crimped Lead Only  
 Connector to Connector Mini-Fit Jr.-to-Pigtail  
 Overview [Off-the-Shelf Pre-Crimped Leads](#)  
 Product Name Mini-Fit Jr.  
 UPC 193264559299

**Physical**

Cable Length 75.00mm  
 Circuits (Loaded) 1  
 Color - Resin Black  
 Gender Female-Pigtail  
 Material - Metal Brass  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 1.270/g  
 Packaging Type Bag  
 Single Ended Yes  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 1.80-3.10mm  
 Wire Size AWG 20  
 Wire/Cable Type UL 1015

**Electrical**

Current - Maximum per Contact 9.0A  
 Voltage - Maximum 600V

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing 2153411101-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2020)4578-DC (25  
 June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[215341](#) Series

**Use With**

Mini-Fit Jr. Receptacle Housing [5557](#)  
 <br>Mini-Fit BMI Slide and Lock Panel  
 Mount [44516](#) <br>Mini-Fit BMI Panel Mount  
 Receptacle Housing<br> [42474](#) , [43760](#)