

EAN:	4013288217608	Size:	275x175x60 mm
Part number:	05105623001	Weight:	921 g
Article number:	Kraftform 300/7 Set 1	Country of origin:	CZ
		Customs tariff number:	82054000

- 7-piece set in compact, textile box with Wera 2go compatibility
- Take it easy tool finder: colour coding according to profile and size
- Lasertip tips for more secure fit in the screw head
- Multi-component Kraftform handle for fast and ergonomic screwdriving
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer

7-piece screwdriver set with Kraftform Plus handle for comfortable ergonomic screwdriving, which avoids blisters and calluses. Hard handle zones for high working speeds, while soft handle zones guarantee a high torque transfer. Includes some tools with Lasertip blades: The tip clings to the screw head and prevents it slipping out. Take it easy tool finder with colour coding and size stamping - for easy and fast location of the required tool. The anti-roll protection avoids bits from annoying rolling away in the workplace.




Web link



https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_kraftform_300_7_set_1.html

Wera - Kraftform 300/7 Set 1
05105623001 - 4013288217608

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

	350 PH 05008710001 1 x PH 1 x 80 mm 05008720001 1 x PH 2 x 100 mm
	367 TORX® 05028008001 1 x TX 15 x 80 mm 05028010001 1 x TX 20 x 100 mm 05028012001 1 x TX 25 x 100 mm
	K240 11990178 1 x 240 x 50 mm

	355 PZ 05009315001 1 x PZ 2 x 100 mm
	335 05110004001 1 x 0.8 x 4 x 100 mm

Suitable for Wera 2go



Kraftform Plus screwdrivers – ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



Suitable for docking with the Wera 2go system.

Lasertip prevents slipping out



It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally "bites" itself firmly into the screw head. Slipping out becomes a thing of the past.

Lasertip



A precisely-focused laser creates a sharp-edged surface structure. This laser treatment results in an edge hardness of up to 1000 HV 0.3. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_kraftform_300_7_set_1.html

Wera - Kraftform 300/7 Set 1
05105623001 - 4013288217608

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Reduced contact pressure



Wera Lasertip reduces the contact pressure required and enhances force transfer – meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

Prevents hand injuries




The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels across the hand.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_kraftform_300_7_set_1.html

Wera - Kraftform 300/7 Set 1
05105623001 - 4013288217608

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de