


**SPECIFICATION  
CONTROL DRAWING  
Crystal Resonator**

FREQUENCY
7.372800MHz



Holder Style	HC-49/U
Mode	Fundamental
Adjustment Tolerance	± 30PPM at 25°C
Temperature Stability	± 50 PPM
Operating Temp. Range	-20°C to +70°C
Load Capacitance	30 pF
ESR	40 Ohm
Marking	Mark AELX027L\FREQ+WWYY

Amdt Date	Change Note	AEL Code	
		X7M372800L027	
		Issue Ref	A