

# E Series Bootlace Ferrules

**multicomp** PRO




## Features

- A range of cable ferrules designed to provide a neat end termination to multi-stranded wires.
- They provide a secure connection to terminal blocks and captive terminals and stop wire strands short circuit to adjacent connectors.
- Crimping is achieved by the action of the screw in the connector, or by use of a dedicated crimping tool.
- The ferrules consist of a tinned copper hollow tube and are also available with a plastic colour coded insulating shroud.

## Specifications

Terminal : Copper 0.3 $\mu$  tin plated  
 Shroud : Nylon  
 Maximum Temperature : 105°C

## Diagram



## Part Number Table

Description	Colour	Wire Size (mm <sup>2</sup> )	L (mm)	C (mm)	C (mm)	A $\pm$ 0.2 (mm)	Part Number
Bootlace Ferrules	Violet	0.25	8	0.8	1.1	12.4	E0208-VIOLET
	Pink	0.34					E0308-PINK
	Blue	0.75	12	1.2	1.5	18.3	E7512-BLUE-L
	Red	1		1.4	1.7		E1012-RED-L
	Black	1.5	18	1.7	2	24.3	E1518-BLACK-L
	Grey	2.5		2.3	2.6	25.4	E2518-GREY
	Orange	4		2.8	3.2		E4018-ORANGE
	Green	6		3.5	3.9	26.5	E6018-GREEN
	Black	25	16	7.5	7.9	28	E25-16-BLACK
	Red	35	25	8.3	8.7	39	E35-25-RED

Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 Element14.com/multicomp-pro

**multicomp** PRO

# E Series

## Bootlace Ferrules

**multicomp** PRO

Description	Colour	Wire Size (mm <sup>2</sup> )	L (mm)	C (mm)	C (mm)	A ±0.2 (mm)	Part Number
Bootlace Ferrules	White	0.75	12	1.2	1.5	18.3	E7512-WHITE-L
	Yellow	1		1.4	1.7		E1012-YELLOW-L
	Red	1.5	18	1.7	2	24.3	E1518-RED-L
	Blue	2.5		2.3	2.6	25.4	E2518-BLUE
	Grey	4	12	2.8	3.2	19.4	E4012-GREY
			18			25.4	E4018-GREY
	Black	6	12	3.5	3.9	20.5	E6012-BLACK
			18			26.5	E6018-BLACK
	Ivory	10	12	4.5	4.9	20.8	E10-12-IVORY
	Green	16		5.8	6.2	26.8	E16-12-GREEN
Brown	25	16	7.5	7.9	28	E25-16-BROWN	

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 Element14.com/multicomp-pro

**multicomp** PRO