




SKINTOP® MS, MS-XL

Brass cable gland



Application

Suitable for use in manufacturing of machinery and equipment, in measuring and controlling technology, in chemical technology, in system manufacturing, in medico-technical equipment and in many other fields where exceptional stability and safe functioning are required.

Advantages:

- solid locked plastic clamp cage
- very economical due to less varieties on stock

Special Feature

Additionally we offer our proven SKINTOP® MS with long connection thread, PG 7-21 with 12 mm and PG 29 with 15 mm for thick wall housings.

Note

Suitable accessories see [[1038]].

Technical Data

Material: Körper: Messing vernickelt Einsatz: Polyamid Dichtring: CR/NBR O-Ring: NBR	Temperature range: -30°C bis +100°C	Protection class: IP 68 - 5 bar	Attention Einbaumaße und Anzugsdrehmomente siehe T21
--	---	---	--

Part-Number	Type-PG-size	Clamping range	ØF mm	Wrench Size mm	C mm	D mm	PU pieces
-------------	--------------	----------------	-------	----------------	------	------	-----------

For a quotation please click on a part number

SKINTOP® MS

5201 5700	MS 7	2 - 6,5		14	25	5	100
5201 5710	MS 9	3 - 8		17	29	6	100
<u>5201 5720</u>	MS 11	4 - 10		20	32	6	50
5201 5730	MS 13,5	5 - 12		22	34	6,5	50
5201 5740	MS 16	8 - 14		24	35	6,5	50
5201 5750	MS 21	11 - 18		30	40	7	25
5201 5760	MS 29	16 - 25		40	48	8	25
5201 5765	MS 36	19 - 32		50	62	15	10
5201 5766	MS 42	28 - 38		57	62	15	5
5201 5767	MS 48	34 - 44		64	62	15	5

