

105 Key Sealed IP68 Antibacterial Medical Keyboard



Order Code: KYB-MED-VALUE-UW (USB WHITE), KYB-MED-VALUE-UB (USB BLACK)
Accuratus AccuMed Value - USB 105 Key Sealed Washable IP68 Medical / Clinical Keyboard



About

The Accuratus Accumed range of medical grade keyboards & mice are specifically designed for environments which have to meet very high hygienic requirements such as hospitals, dental practices, cosmetic surgeries, doctors, vets, laboratories and in food & pharmaceutical production areas. Not only could these keyboards be used in hygienic areas, they would also be perfect in dusty, dirty and wet situations like workshops, boats and in vehicles. Our Accumed range have all been designed so that there are no areas around the keys and buttons where dirt and germs can collect, the AccuMed Value is quick and easy to wipe clean, the perfect combination to aid with bacteria, virus, fungi and algae control.

Specifications

- USB interface (PS/2 also available)
- Available in black or pure white, other colours made on request
- Full UK 105 key layout
- Fully sealed IP68 design, 100% waterproof
- Compatible with all hospital disinfectants
- Clear and easy to read key legends
- Internal key structure is plastic for enhanced durability and feel
- Keys have a tactile feel to allow for comfortable and natural typing
- Durable rigid silicone body with internal plastic structure.
- Silicone casing, internal ABS keycaps and internal top housing, with HIPS bottom case
- Designed so that there are no areas around keys that dirt and germs can collect
- Easy to clean with a wet cloth or in water
- Rigid keyboard with sealed silicone coating
- Fully sealed silicone casing, dust, water and chemical resistant, IP68 rated
- Status LED's (Caps, Num & Scroll Lock)
- Brown/white box environment friendly packaging



Physical Specifications

- Dimensions: 439 x 142 x 25.2 mm (l x w x h)
- Weight: 550g



ACCURATUS