



RSD1QP

▶ RSD REMOTE DISPLAY FOR SENSOR PRODUCTS





RSD Series Remote Display
 Single Sensor Support
 Output: Depends on Sensor
 Euro 5-pin 150 mm (6 in) PVC Pigtail
 Part Number: 804095








CERTIFICATIONS






COMPATIBLE PRODUCTS

DOUBLE-ENDED CORDSETS

	<p>MQDC-4501SS</p> <p>Euro-Style QD to Euro-Style QD
5-pin Euro Straight Male; 4-pin Euro Straight Female
0.3 m (1.0 ft) in Length
Nickel-Plated Brass Coupling Nuts; PVC Jacketed Cable
4x22AWG Conductors; No Shield</p>
	<p>MQDC-4506SS</p> <p>Euro-style QD to Euro-style QD
5 Pin Euro Straight Male; 4 Pin Euro Straight Female
1.83 m (6.0 ft) in Length
Nickel-Plated Brass Coupling Nuts; PVC Jacketed Cable; 4x22AWG Conductors; No Shield</p>
	<p>MQDC-4B5G01SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Female Connector Straight
5-pin Male Connector Straight 0.3 m Length
Nickel plated brass coupling nut</p>

	<p>MQDC-4B5G06SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 4-pin Female Connector Straight
5-pin Male Connector Straight 2 m Length
Nickel plated brass coupling nut</p>
	<p>MQDC-5401SS</p> <p>Euro-style QD to Euro-style QD
5 Pin Euro Straight Female; 4 Pin Euro Straight Male
0.3 m (1.0 ft) in Length
Nickel-Plated Brass Coupling Nuts; PVC Jacketed Cable; 4x22AWG Conductors; No Shield</p>
	<p>MQDC-5406SS</p> <p>MQDC-5406SS-800754</p>
	<p>MQDEC3-503SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 5-pin Male Connector Straight
5-pin Female Connector Straight 0.91 m Length
Chrome plated brass coupling nut; Shield wire grounded to coupling nut</p>
	<p>MQDEC3-506SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 5-pin Male Connector Straight
5-pin Female Connector Straight 1.83 m Length
Chrome Plated Brass Coupling Nut; Shield Wire Grounded to Coupling Nut</p>
	<p>MQDEC3-515SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 5-pin Male Connector Straight
5-pin Female Connector Straight 4.58 m Length
Chrome plated brass coupling nut; Shield wire grounded to coupling nut</p>
	<p>MQDEC3-530SS</p> <p>Euro-style Quick Disconnect Cable
Double-ended 5-pin Male Connector Straight
5-pin Female Connector Straight 9.2 m Length
Chrome plated brass coupling nut; Shield wire grounded to coupling nut</p>

SINGLE-ENDED CORDSETS

	<p>MQDEC2-506</p> <p>Euro-Style Quick Disconnect Cable with Shield
5-Pin Straight Connector
2 m (6.5 ft) in Length
Chrome-plated brass coupling nut</p>
	<p>MQDEC2-515</p> <p>Euro-Style Quick Disconnect Cable with Shield
5-Pin Straight Connector
5 m (15 ft) in Length
Chrome-plated brass coupling nut</p>
	<p>MQDEC2-530</p> <p>Euro-Style Quick Disconnect Cable with Shield
5-Pin Straight Connector.C
9 m (30 ft) in Length
Chrome-plated brass coupling nut</p>



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America