

Product Specification PDF

Date	Correct as of 21st Sep 2020
Brand	C.K
Product	T9735USB
Description	10W Rechargeable LED Site Light
Barcode	5013969246599
Commodity code	9405403990
Country of origin	CN



Features & Benefits	~ High Power COB LED ~ 700 Lumens ~ 2 Lighting modes: High, Dimmed ~ Battery life: High: 2.5hrs, Dimmed: 4hrs ~ 3 hours approximate charge time ~ 360° adjustable head directs the light where you need it ~ Impact resistant, tested to IK05 ~ Water & dirt resistant, tested to IP65 ~ Including rechargeable 3.7V 2200mAh Li-Ion battery
Applicable Standards	CE, IP65, WEEE, RoHS
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	20
Width mm	110	200	320	430
Depth mm	35	35	210	320
Height mm	115	220	215	240
Weight	213	287	3100	6.8
Packaging Information	Card use	Card	Box	carton
	Card gms	25	230	600
	Plastic use	Blister	0	-
	Plastic gms	12	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0