

# Tab E7 ZA400059GB

**Product**

Lenovo TB-7104F

**Region**

UKI

**Country/Region**

United Kingdom

**Machine Type**

ZA40

**TopSeller**

No

**Processor**

MediaTek MT8167A/D (4C, 4x A35 @1.3GHz)

**Graphics**

Integrated IMG GE8300 GPU

**Chipset**

MediaTek SoC Platform

**Memory**

1GB Soldered

**Display**

7" WSVGA (1024x600) TN 250nits

**Touchscreen**

5-point Multi-touch

**Expandable Memory**

MicroSD card (Up to 128GB)

**Storage**

16GB eMCP

**WLAN + Bluetooth**

11b/g/n, 1x1 + BT4.0

**WWAN**

None

**Card Slot**

MicroSD Card Holder Tray

**Bundled Accessories**

None

**Color**

Slate Black

**Case Material**

Plastic

**Camera**

Front 0.3MP / Rear 2.0MP

**Microphone**

Mono

**VoiceCall**

No

**Battery**

Integrated 2750mAh

**Power Adapter**

5V / 1.0A

**Operating System**

Android Oreo

**Bundled Service**

Not Available

**Base Warranty**

1-year, Depot

**End of Support**

Not Available

**EAN / UPC / JAN**

192940710979

**Announce Date**

2019-01-01

**Notes:**

**Battery life** is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

 [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.


Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.



© Lenovo, 2020. All rights reserved.



# Lenovo Tab E7 Platform Specifications

Product Specifications Reference (PSREF)



Processor	MediaTek® Processor <b>MT8167A/D</b> for WiFi models - Lenovo TB-7104F 32-bit Quad-Core Processor (ARM Cortex-A35, up to 1.3GHz) <b>MT8321A/D</b> for 3G models - Lenovo TB-7104I 32-bit Quad-Core Processor (ARM Cortex-A7, up to 1.3GHz)	Dimensions Weight Case color Case material	<i>WxHxT:</i> 7.6" x 4.35" x 0.41"; 193.2mm x 110.54mm x 10.35mm 0.6lb / 271.7g Slate black Plastic
Graphics	WiFi model : Integrated IMG GE8300 GPU 3G model : Integrated ARM Mali-400 GPU	Ports	One Micro USB 2.0, audio combo jack, one MicroSD card slot (WiFi model) or Dual cards slot for SIM card and MicroSD card (3G model) <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>
Display	7" (178mm) WSVGA (1024x600), TN, color depth 16.7M, color gamut 50%, 250 nits	Camera	<i>Front camera:</i> 0.3-megapixel, VGA <i>Rear camera:</i> 2.0-megapixel, fixed focus
Multi-touch	Capacitive-type multi-touch, support 5 fingers	Audio support	Single speaker / single microphone, 3.5mm combo audio / microphone jack
Memory	Max 1GB / LPDDR3, soldered to systemboard	Keyboard	None
Storage	8GB or 16GB eMCP (embedded Multi-Chip Package) flash memory on board	Touchpad	None
Card slot	WiFi model : MicroSD card slot, support FAT32 up to 128GB 3G model : Dual cards slot, support single Nano-SIM card or Nano-SIM card + MicroSD card (up to 128GB)	Bundled Accy	<i>Optional:</i> Back Cover and Film
 <p style="text-align: center;">WiFi model</p>  <p style="text-align: center;">3G model</p>		Security chip	None
		Fingerprint reader	None
		VoiceCall (opt)	Support voice call, only on 3G model
		Battery	Li-ion Polymer 2750mAh
		Max battery life	Standby Time : Up to 250 hrs Video (720p) playback Time : 5 hrs Browsing Time: 5 hrs <i>* Battery life varies significantly with hardware configurations, settings, usage, &amp; other factors</i>
		AC adapter	5V/1A AC adapter
		Preload	Android® Oreo (Go Edition) Preloaded applications (only some listed) <ul style="list-style-type: none"> <li>• Launcher</li> <li>• Phone</li> <li>• Messaging</li> <li>• Contacts</li> <li>• System Update</li> <li>• FM Radio</li> <li>• OOBE</li> <li>• Recorder</li> <li>• Notification Center</li> <li>• Google Calendar</li> </ul>
Ethernet	None	Limited warranty	<i>One of the following, configurable by model:</i> <ul style="list-style-type: none"> <li>• 3-month mail-in service</li> <li>• 1-year mail-in service</li> <li>• 2-year/1-yr battery mail-in service</li> <li>• 1-year courier / depot service</li> <li>• 2-year/1-yr battery courier / depot service</li> <li>• 1-year customer carry-in service</li> <li>• 2-year/1-yr battery customer carry-in service</li> <li>• 2-year/1-yr battery courier / depot or customer carry-in service</li> </ul>
WLAN	802.11 /b/g/n, 1x1, single band (2.4 GHz)	Environment	RoHS-compliant
Bluetooth®	Bluetooth 4.0		
WWAN (optional)	3G WCDMA connectivity		
LTE Band	GSM: B2/3/5/8 UMTS: B1/2/5/8		
NFC	None		
GPS	GPS (3G model only)		
A-GPS	A-GPS (3G model only)		
WiFi Direct	WiFi Direct		
WiFi Display	WiFi Display (WiFi model only)		
FM Radio	FM Radio (3G model only)		
Vibrator	Vibrator (3G model only)		
G-sensor	G-sensor		
P-sensor	None		
L-sensor	None		
E-compass	None		
Hall Sensor	None		
Gyroscope	None		
Proofing	None		

Note: The specifications above may not be available in all regions

Lenovo  
March 2020

