

Tab M8 FHD (2nd Gen) ZA5F0006GB

Product

Lenovo TB-8705F

Region

UKI

Country/Region

United Kingdom

Machine Type

ZA5F

TopSeller

No

Processor

MediaTek Helio P22T (8C, 8x A53 @2.3GHz)

Graphics

Integrated IMG GE8320 GPU

Chipset

MediaTek SoC Platform

Memory

3GB Soldered

Display

8" FHD (1920x1200) IPS 350nits

Touchscreen

10-point Multi-touch

Storage

32GB eMMC

Expandable Memory

MicroSD card (Up to 256GB)

WLAN + Bluetooth

11a/b/g/n/ac, 1x1 + BT5.0

WWAN

None

Card Slot

MicroSD Card Holder Tray

Bundled Accessories

None

Case Material

Metal / Plastic

Color

Platinum Grey

Camera

Front 5.0MP / Rear 13.0MP

Microphone

Mono

VoiceCall

No

Battery

Integrated 5000mAh

Power Adapter

5V / 2.0A

Operating System

Android Pie

Bundled Service

Not Available

Base Warranty

1-year, Depot

End of Support

Not Available

EAN / UPC / JAN

193638812159

Announce Date

2019-09-03

Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo Tab M8 FHD (2nd Gen) Platform Specifications

Product Specifications Reference (PSREF)



Processor	MediaTek® Processor MediaTek Helio P22T (8xARM Cortex-A53, up to 2.3GHz)								
Graphics	Integrated IMG GE8320 GPU								
Display	Size	Resolution	Type	Brightness	Color Gamut	Viewing Angle			
	8" (203.2mm)	FHD (1920 x 1200)	WVA	Typ. 350nits Min. 320nits	Typ. 60% Min. 55%	160°			
Multi-touch	TDDI, Capacitive-type multi-touch, Anti-Fingerprint (AF) Coating, supports 10-point touch, glove-touch, and wet finger touch								
Memory	3GB or 4GB / LPDDR3, soldered to systemboard								
Storage	32GB or 64GB eMMC (Embedded Multi Media Card), flash memory on board								
Card slot	One single card slot (WiFi model) or one dual-card slot (LTE model), supports Nano-SIM card + MicroSD/TF card (Up to 256GB, FAT32)								
Bluetooth®	Bluetooth 5.0								
WLAN	802.11 a/b/g/n/ac, 1x1, 2.4 GHz / 5 GHz Wi-Fi Dual Bands								
WWAN (Optional)	4G LTE connectivity								
LTE Band	GSM:	B2/B3/B5/B8							
	WCDMA:	B1/B2/B5(B6/B19)/B8							
	FDD LTE:	B1/B2/B3/B4/B5(B19)/B7/B8/B20							
	TDD LTE:	B38/B40							
NFC	None								
WiFi Direct	Yes								
WiFi Display	Yes								
WHDI	None								
FM Radio	Yes								
A-GPS (Optional)	Yes								
GPS	Yes								
Glonass	Yes								
Beidou	Yes								
Vibrator (Opt)	Yes								
G-sensor	Accelerometer sensor								
P-sensor	Proximity sensor								
L-sensor	Ambient sensor								
E-compass	None								
Hall Sensor	None								
Gyroscope	None								
Proofing	IP52								
Dimensions	WxDxH: 7.80" x 4.83" x 0.32"; 198.2mm x 122.6mm x 8.15mm								
Weight	305g / 0.67lb								
Case color	Platinum Grey								
Case material	Metal/Plastic for back cover								
Ports	One Micro-USB 2.0, supports Lenovo T-Hub, OTG, 3.5mm (0.14inch) combo audio / microphone jack, one MicroSD/TF slot or dual-card slot for Nano-SIM card and MicroSD/TF card <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>								
Buttons	Power key, volume key								
Bundled Accy	None								
Camera	Front / Focus Mode	5.0MP	Fixed Focus	Rear / Focus Mode	13.0MP	Auto Focus	Type CMOS	Zoom Digital	Flash Light Yes
Audio	Single side speaker with Dolby Audio® / single microphone (mono), 3.5mm (0.14inch) combo audio / microphone jack (CTIA)								
Keyboard	None								
Touchpad	None								
Security chip	None								
Fingerprint reader	None								
VoiceCall (Opt)	VoiceCall								
Battery type	Li-ion Polymer 5000mAh (Minimum) / 5100mAh (Typical)								
Battery life	Standby Time: Over 2wks Online Video playback Time: Up to 12hrs Browsing Time: Up to 18hrs <i>* Battery life varies significantly with hardware configurations, settings, usage, & other factors</i>								
AC adapter	5V/2A								
Charging time	Over 3.3hrs								
Preload	Android® Pie			Lenovo applications			Third-party applications		
	<ul style="list-style-type: none"> Camera FM Radio Tablet Manager 			<ul style="list-style-type: none"> Google Maps Gmail YouTube Messages (TB-8505F) Phone (TB-8505F) Google Chrome Google Photos Duo Calendar Files Netflix (ROW version) 			<i>* Applications vary from different Android Pie versions</i>		
Limited warranty	One of the following, configurable by model: <ul style="list-style-type: none"> 1-year mail-in service 2-year/1-yr battery mail-in service 1-year courier / depot service 2-year/1-yr battery courier / depot service 1-year customer carry-in service 2-year/1-yr battery customer carry-in service 2-year/1-yr battery courier / depot or customer carry-in service 								
Environment	RoHS-compliant								

The specifications above may not be available in all regions and might change by region.

Lenovo
July 2020

Tab M8 FHD (2nd Gen)

