



#23764

Customisable Gaming Mouse

High-accuracy gaming mouse with RGB lighting and interchangeable side plates

Key features

- Advanced optical sensor with resolution up to 10.000 DPI
- 4 magnetically interchangeable side plates to customise side buttons and shape
- 2 left-side plates with 3 or 9-button configurations, programmable for any game
- 2 right-side plates with different shapes
- Fully adjustable RGB lighting with multiple effects
- Up to 14 independently programmable buttons



What's in the box

- Gaming mouse
- 4 side plates

System requirements

- Windows 10, 8 or 7
- USB port



16.8M
COLOURS



10.000 DPI
SENSOR



4
ADJUSTABLE
SIDE PLATES



FOR FPS, MMO
& MOBA



Customised Gaming Control

A gaming mouse has the biggest impact with even the smallest of movement, so it better be meticulous. Imagine a mouse so meticulous that it's fully attuned to your gaming style and does exactly what you want. A customisable mouse makes that dream a reality; the Trust GXT 970 Morfix Customisable Gaming Mouse can be tailored to your unique gaming preferences.

Tailored Side Plates

Enjoy a personalised experience with four magnetically interchangeable side plates. With a diverse choice of side-buttons and plate shapes, you can design your unique weapon of choice. The included two plates on the left have 3 and 9 buttons, programmable for any game – whether that's a shooter, MOBA, battle royale, RTS or MMORPG. The plates on the right feature different shapes to suit your design preferences.



Program your Victory

With 14 independently programmable buttons (depending on the side plate of choice) you can be sure of a truly customised experience. The advanced software enables you to program buttons and macros, allowing you to launch up to 168 actions with a single click. You can even customise your light settings.

Accuracy at Hand

The Trust GXT 970 Morfix Customisable Gaming Mouse is fitted with an advanced optical sensor with a resolution of up to 10,000 DPI, giving you greater control. The highly accurate sensor ensures precise control over your mouse movement. What's more, the DPI level is indicated by a specific coloured LED light, so you can keep an eye on your settings.





Light the Way

Customised gameplay is enhanced by the RGB light experience. With adjustable RGB lighting you can select your favourite light mode. Choose between breathing, jumping and other light effect modes or select your war hue from the full RGB range, featuring over 16 million colours.

GENERAL

Formfactor	Standard	Ergonomic design	True
Height of main product (in mm)	42 mm	Width of main product (in mm)	72 mm
Depth of main product (in mm)	126 mm	Total weight	167 g
Weight of main unit	110 g		

CONNECTIVITY

Connection type	Wired	Bluetooth	False
USB version	2.0	Connector type	USB-A male

GAMING

Designed for gaming	True
----------------------------	------

SENSOR

DPI	800, 1600, 2400, 3200, 4000, 5000	DPI range	200 - 10000 dpi
Max. DPI	10.000 dpi	DPI adjustable	True
Sensor technology	Optical	Sensor model	PMW3325
Polling rate	125/250/500/1000Hz		

LIGHTING

Lights	True
---------------	------

CONTROL

Grip type	Finger, palm	Left-right handed use	Right-handed
Scroll wheel	True	Trackball	False
Horizontal scrolling	False	Controls	Backward, dpi +, dpi -, forward, left, mid, right, special buttons
Number of buttons	14	DPI button	True
Programmable buttons	True	Adjustable weight	False
Suitable surface	Non-reflective flat surface		

INPUT

Power source	USB
---------------------	-----

FEATURES

Silent click	False	On-board memory	True
Gliding pads	UPE	Software	True
Special features	2 extra side pieces		

COMPATIBILITY

Compatible Device Types Laptop, pc

**Compatible Software
Platforms**


Windows




PRODUCT VISUAL 1




PRODUCT PICTORIAL 1



PRODUCT PICTORIAL 2



PRODUCT PICTORIAL 3



PRODUCT PICTORIAL 4



PRODUCT PICTORIAL 5



PRODUCT ESHOT 1



PRODUCT VISUAL 2



PRODUCT VISUAL 3



PRODUCT VISUAL 4



PRODUCT VISUAL 5



PRODUCT VISUAL 6