



#23758

Lightweight RGB Gaming Mouse

Lightweight RGB illuminated gaming mouse with honeycomb shell

Key features

- 74 grams lightweight honeycomb shell housing for fast mouse response
- High precision optical sensor up to 10,000 DPI
- Up to 1000Hz adjustable polling rate for high responsive control
- Customizable RGB lighting incl breathing and rainbow effect
- Zero drag braided cable ensures smooth movement
- Includes 2 easy to reach thumb buttons





What's in the box

- Gaming mouse
- User guide

System requirements

- Windows 10, 8 or 7
- Chrome OS
- USB port





Speed Is Everything

When you're out on the battlefield, you don't have time to think. That's why you need a mouse that can keep up. The Trust Gaming GXT 960 Graphin is lightweight, blazing fast and has an adjustable polling rate of up to 1000Hz. It's durable, uses ultra-low friction gliding pads for smooth movement and has a unique identity due the RGB lighting. Shoot first, ask questions later.

Float Like a Butterfly

When you've got the weight of your teammates on your shoulders, you don't want the weight of your mouse slowing you down. The GXT 960 Graphin weighs only 74 grams thanks to its honeycomb shell housing. Combined with the polling rate of up to 1000Hz, the adjustable resolution of up to 10,000 DPI and the ultra-low friction gliding pads, you will have the advantage over your opponents.



Sting Like a Bee

But speed can only get you so far; your equipment needs to be reliable. The zero drag braided cable makes sure you will move your mouse around freely, without having to worry about it getting jammed behind something on your desk. Also, the Graphin has two easy to reach thumb buttons giving you complete control over your games, while the two main buttons inspire you to keep your finger on the trigger.

While Looking Fabulous

The honeycomb design isn't just useful, it gives the GXT 960 Graphin a unique look, too. Adjust the RGB lighting to your liking with the advanced software and show the world who it is they're dealing with. The next time you go to a LAN party, they'll be sure to remember you.



GENERAL

Formfactor	Standard	Ergonomic design	False
Height of main product (in mm)	40 mm	Width of main product (in mm)	63 mm
Depth of main product (in mm)	126 mm	Total weight	106 g
Weight of main unit	74 g		

CONNECTIVITY

Connection type	Wired	Bluetooth	False
USB version	2.0	Connector type	USB-A male

GAMING

Designed for gaming	True
----------------------------	------

LIGHTING

Lights	True
---------------	------

SENSOR

DPI range	200 - 10000 dpi	Max. DPI	10.000 dpi
DPI adjustable	True	Sensor technology	Optical

CONTROL

Grip type	Claw, finger, palm	Left-right handed use	Right-handed
Scroll wheel	True	Trackball	False
Horizontal scrolling	False	Controls	Backward, dpi loop, forward, left, mid, right
Number of buttons	6	DPI button	True
Programmable buttons	True	Adjustable weight	False
Suitable surface	Non-reflective flat surface		

INPUT

Power source	USB
---------------------	-----

FEATURES

Silent click	False	Gliding pads	Teflon
Software	True		

COMPATIBILITY

Compatible Device Types	Laptop, pc	Compatible Software Platforms	Windows
--------------------------------	------------	--------------------------------------	---------



PRODUCT VISUAL 1



PRODUCT PICTORIAL 1



PRODUCT PICTORIAL 2



PRODUCT PICTORIAL 3



PRODUCT PICTORIAL 4



PRODUCT ESHOT 1



LIFESTYLE VISUAL 1



LIFESTYLE VISUAL 2



PRODUCT SIDE 1



PRODUCT TOP 1



PRODUCT EXTRA 1



PRODUCT EXTRA 2