

## Datasheet

**IEC PTFE Insulated Twin Twisted Pair Thermocouple Cable**


- PTFE twin twisted pair for extending or making simple thermocouples
- Single pair of PTFE insulated conductors twisted together
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Suitable for steam & pressure applications, autoclaves, sterilizers etc.
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour coded to IEC-584-3

Type	Conductors	Reel Length	Manufacturers Code	Order Code
J	1/0.2mm	25m	WJ-244-D	<b>XF-242-FAR</b>
J	1/0.2mm	50m	WJ-244-D	<b>XF-1261-FAR</b>
J	1/0.315mm	10m	WJ-245-D	<b>XF-1617-FAR</b>
J	1/0.315mm	25m	WJ-245-D	<b>XF-1618-FAR</b>
J	1/0.315mm	50m	WJ-245-D	<b>XF-1619-FAR</b>
J	1/0.315mm	100m	WJ-245-D	<b>XF-1620-FAR</b>
J	1/0.508mm	10m	WJ-246-D	<b>XF-1624-FAR</b>
J	1/0.508mm	25m	WJ-246-D	<b>XF-1621-FAR</b>
J	1/0.508mm	50m	WJ-246-D	<b>XF-1622-FAR</b>
J	1/0.508mm	100m	WJ-246-D	<b>XF-1623-FAR</b>
J	7/0.2mm	10m	WJ-243-D	<b>XF-1613-FAR</b>
J	7/0.2mm	25m	WJ-243-D	<b>XF-1614-FAR</b>
J	7/0.2mm	50m	WJ-243-D	<b>XF-1615-FAR</b>
J	7/0.2mm	100m	WJ-243-D	<b>XF-1616-FAR</b>
K	1/0.2mm	10m	WK-200-D	<b>XF-1308-FAR</b>
K	1/0.2mm	25m	WK-200-D	<b>XF-243-FAR</b>
K	1/0.2mm	50m	WK-200-D	<b>XF-536-FAR</b>
K	1/0.2mm	100m	WK-200-D	<b>XF-537-FAR</b>
K	1/0.315mm	25m	WK-201-D	<b>XF-1263-FAR</b>
K	1/0.315mm	50m	WK-201-D	<b>XF-1256-FAR</b>
K	1/0.508mm	25m	WK-202-D	<b>XF-1268-FAR</b>
K	1/0.508mm	50m	WK-202-D	<b>XF-1251-FAR</b>
K	7/0.2mm	10m	WK-303-D	<b>XF-1654-FAR</b>
K	7/0.2mm	25m	WK-303-D	<b>XF-1653-FAR</b>
K	7/0.2mm	50m	WK-303-D	<b>XF-1655-FAR</b>
T	1/0.2mm	10m	WT-300-D	<b>XF-1267-FAR</b>
T	1/0.2mm	25m	WT-300-D	<b>XF-244-FAR</b>
T	1/0.2mm	50m	WT-300-D	<b>XF-538-FAR</b>
T	1/0.2mm	100m	WT-300-D	<b>XF-539-FAR</b>

T	1/0.315mm	10m	WT-301-D	<b>XF-1695-FAR</b>
T	1/0.315mm	25m	WT-301-D	<b>XF-1693-FAR</b>
T	1/0.315mm	50m	WT-301-D	<b>XF-1694-FAR</b>
T	1/0.315mm	100m	WT-301-D	<b>XF-1696-FAR</b>
T	7/0.2mm	10m	WT-303-D	<b>XF-1702-FAR</b>
T	7/0.2mm	25m	WT-303-D	<b>XF-1701-FAR</b>
T	7/0.2mm	50m	WT-303-D	<b>XF-1703-FAR</b>
T	7/0.2mm	100m	WT-303-D	<b>XF-1704-FAR</b>

