

### SPECIFICATION SHEET

PRODUCT CODE: 778319

Increase your home security and add a little style with this ultra-modern LED Garden Bollard light. The light is dispersed from the sides, creating a beautiful lighting effect suitable for any garden, driveway or parking space. The tough stainless-steel body ensures the bollard light is able to withstand all weather conditions. With an IP44 rating, the garden lantern is suitable for an ES/E27 LED lamp with a maximum 15W power.



ES/E27 FITTING



NON-DIMMABLE




IP44 RATING



MAX WATTAGE

### SPECIFICATION

Product code	778319
Fitting	Garden Bollard
Bulb shape	ES Edison Screw (E27)
Max Wattage	15W
Dimmable	No
CCT	No
Width	125mm
Height	500mm
Depth	120mm
Input frequency	50Hz
Voltage	220-240V
Material	Stainless Steel + PC Cover
Packaging	White Box + Colour Label
IP Rating	IP44



TIME LED is part of Pitacs Limited

Bradbourne Point, Bradbourne Drive, Tilbrook, Milton Keynes, Buckinghamshire MK7 8AT

T: +44 (0)1908 271155 F: +44 (0)1908 640017 E: info@timeled.co.uk W: www.timeled.co.uk



October 2019