

Datasheet

IEC Type J PFA Exposed Welded Tip Thermocouples with Miniature Thermocouple Plug



- Thermocouple type J to IEC 584
- Fast response, welded exposed junction
- Teflon® PFA insulated twin-twisted lead
- Class 1 cable specification in accordance with BS EN 60584-3:2008
- Tolerance to IEC 584 Class 1
- Miniature plug termination
- Temperature range -75°C to +250°C
- Ideal for test & development applications

type	Conductors	Length	Order Code
J	1/0.3mm	1m	XF-1554-FAR
J	1/0.3mm	2m	XF-1555-FAR
J	1/0.3mm	3m	XF-1556-FAR
J	1/0.3mm	5m	XF-1557-FAR
J	1/0.5mm	1m	XF-1558-FAR
J	1/0.5mm	2m	XF-1559-FAR
J	1/0.5mm	3m	XF-1560-FAR
J	1/0.5mm	5m	XF-1561-FAR
J	1/0.5mm	10m	XF-1562-FAR