

Datasheet

IEC Type K or J Crocodile Clip Thermocouple with Fiberglass Stainless Steel Overbraided Cable



- 1 or 3 metres stainless steel over-braided PFA Teflon® cable fitted with miniature plug
- Temperature rating -50°C to +250°C
- Grounded measuring junction

Specifications

Sensor type:	Type K or J thermocouple to IEC 584
Construction:	Thermo-element located in crocodile clip
Cable/Termination:	1 or 3 metres PFA Teflon® insulated with stainless steel over-braid, miniature plug termination
Thermocouple junction:	Grounded on crocodile clip
Temperature range:	-50°C to + 250°C

Type	Length	Order Code
K	1m	XF-1578-FAR
K	3m	XF-1579-FAR
J	1m	XF-1580-FAR
J	3m	XF-1581-FAR