

# DC axial fan

Series 4200 N 119 x 119 x 38 mm



- **General description:** DC fan with electronically commutated external rotor motor. Commutation electronics completely integrated.
- **Impeller material:** Fiberglass-reinforced PA plastic
- **Housing material:** Fiberglass-reinforced PBTP plastic

Nominal data		Voltage	Voltage range VDC	Air flow	Speed	Power consumption	Sound level	Sound pressure level	Ambient temperature	L10 service life at 40 °C	L10 service life at max. temp.	Weight
Type	Motor	VDC	VDC	m³/h	1/min	W	Bel	dB(A)	°C	h	h	kg
4212 NGN	--	12	7 - 14.5	165	2750	4.3	5.4	42	-20 .. 70	60000	30000	0.230

Subject to modification

## Characteristic: Pressure over air flow



