

**Screwdriver
SDIS 0.4X2.0X60**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Type	SDIS 0.4X2.0X60
Order No.	9205690000
Version	Screwdriver, Blade width (B): 2 mm, Blade length: 60 mm, Blade thickness (A): 0.4 mm
GTIN (EAN)	4032248772995
Qty.	1 pc(s).

Creation date September 7, 2020 10:49:43 AM CEST

Catalogue status 05.09.2020 / We reserve the right to make technical changes.

Data sheet

Screwdriver SDIS 0.4X2.0X60

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	164 mm	Width (inches)	6.457 inch
Weight	30 g	Net weight	26 g
Diameter	23 mm		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Screwing tools

Blade length	60 mm	Blade thickness (A)	0.4 mm
Blade type	A	Blade width (B)	2 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
eClass 9.0	21-04-04-07	eClass 9.1	21-04-04-07
eClass 10.0	21-04-04-07	UNSPSC	27-11-17-01

Approvals

Approvals



Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Screwdrivers
Brochure/Catalogue	CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN CAT 1 TERM 16/17 EN