

**HDC enclosures  
HDC IP68 24B FRAME M6**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

**General ordering data**

Type	HDC IP68 24B FRAME M6
Order No.	<a href="#">1110920000</a>
Version	HDC enclosures, Size: 8, Protection degree: IP68, IP69K, , Clamping yoke connection, Standard
GTIN (EAN)	4032248886982
Qty.	1 pc(s).

## HDC enclosures HDC IP68 24B FRAME M6

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

Width	58 mm	Width (inches)	2.283 inch
Height	17 mm	Height (inches)	0.669 inch
Depth	156 mm	Depth (inches)	6.142 inch
Mounting dimension - width	130 mm	Mounting dimension - height	32 mm
Net weight	88 g		

### Temperatures

Limit temperature -50 °C ... 125 °C

### Dimensions

Height of housing B	17 mm	Hole pitch length A2	130 mm
Total length housing	156 mm		

### General data

EMC housings	Yes	Housing main material	diecast aluminium
Protection degree	IP68, IP69K		

### Version

Design	Standard	Design of locking system	Clamping yoke connection
Size	8	Suitable for ModuPlug®	Yes
Top part/bottom part/lid	lower part	Type	Bulkhead (feed-through)

### Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
eClass 9.0	27-44-02-02	eClass 9.1	27-44-02-02
eClass 10.0	27-44-02-02	UNSPSC	30-21-18-01

### Approvals

Approvals



ROHS Conform

### Downloads

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">FL FIELDWIRING EN</a>
Engineering Data	<a href="#">EPLAN</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**HDC enclosures  
HDC IP68 24B FRAME M6**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

