

18V Cordless Brushless Angle Grinder R18AG7-0



BRUSHLESS



- Powerful Brushless 125mm grinder ideal for a variety of cutting and grinding applications
- Brushless motor eliminates friction to provide the power to cut, grind or even work with masonry
- Intelligent electronics constantly regulate the motor to maximise runtime
- Electronic anti-kickback technology shuts the tool down when a jam is detected improving user safety
- 3 position handle for better control when grinding or cutting
- Tool-less wheel guard and nut for easy accessory fitting

Article Number	5133004692
Bore size (mm)	22
Charger included?	No
Disc diameter (mm)	125
EAN Code	4892210184146
No load speed (rpm)	11000
No. of batteries supplied	0
Power	18V
Sound power level (Lwa)(dB(A))	91.0
Sound power level uncertainty [dB[A]]	3.0
Sound pressure level (Lpa)(dB(A))	80.0
Sound pressure level uncertainty [dB[A]]	3.0
Spindle size	M14
Standard equipment	Auxiliary handle, wheel guard, 1 x grinding disc
Supplied in	Recyclable Carton
Vibration grinding [m/s ²]	3.9
Vibration grinding uncertainty [m/s ²]	1.5
Weight [without battery] [Kg]	2.2
Weight with battery pack (kg)	2.6

*Registration required for extension from 2-3 years. Please visit our site for full [T&C's](#)