

# 18V Cordless SDS+ Rotary Hammer Drill R18SDS-0

# RYOBI®



- Pneumatic hammer drill ideal for drilling holes in stone and concrete
- SDS+ chuck for fast drilling and easy accessory bit changes
- 4 modes for extra versatility (hammer drill, rotary drill, chisel, chisel alignment)
- Chisel function ideal for applications such as light tile removal
- Pneumatic hammer mechanism delivers 1.3J of impact energy making it easy to drill in hard materials like concrete
- LED lights up your work area for better visibility

Article Number	5133004685
Charger included?	No
Charging time	-
EAN Code	4892210184757
Impact rate (ipm)	0-5000
Max drilling steel (mm)	13
Max. drilling masonry (mm)	16
Max. drilling wood (mm)	16
Max. torque (Nm)	15
No load speed (rpm)	0-1300
No. of batteries supplied	0
Power	18V
Sound power level (Lwa)(dB(A))	96.2
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level (Lpa)(dB(A))	85.2
Sound pressure level uncertainty [dB(A)]	3.0
Standard equipment	None
Supplied in	Recyclable Carton
Vibration chiseling (m/s <sup>2</sup> )	11.7
Vibration chiselling uncertainty [m/s <sup>2</sup> ]	1.5
Vibration drilling into concrete [m/s <sup>2</sup> ]	14.1
Vibration drilling into concrete uncertainty [m/s <sup>2</sup> ]	1.5
Weight [without battery] [Kg]	1.7
Weight with battery pack (kg)	2.1

\*Registration required for extension from 2-3 years. Please visit our site for full [T&C's](#)