

18V Cordless Drill/Driver R18DD3-0

RYOBI®



- Cordless drill driver ideal for drilling in wood or metal and screw driving applications
- 13mm ratcheting chuck for improved bit gripping strength and durability
- 2 gears to control the max speed to match different materials and applications
- 24 torque settings help to drive screws flush every time
- LED lights up your work area for better visibility



Article Number	5133004693
Battery pack capacity (Ah)	-
Battery type	-
Charger included?	No
Charging time	-
Chuck capacity (mm)	13
EAN Code	4892210184153
Max drilling steel (mm)	13
Max. drilling wood (mm)	38
Max. torque (Nm)	50
No load speed (rpm)	0-500 / 0-1800
No. of batteries supplied	0
Power	18V
Sound power level (Lwa)(dB(A))	86.9
Sound power level uncertainty [dB[A]]	3.0
Sound pressure level (Lpa)(dB(A))	75.9
Sound pressure level uncertainty [dB[A]]	3.0
Standard equipment	Double ended bit
Supplied in	Recyclable Carton
Torque settings	24
Vibration drilling into Metal [m/s ²]	<2.5
Vibration drilling into metal uncertainty [m/s ²]	1.5
Vibration screw driving [m/s ²]	<2.5
Vibration screw driving uncertainty [m/s ²]	1.5
Weight [without battery] [Kg]	1.3
Weight with battery pack (kg)	1.7

*Registration required for extension from 2-3 years. Please visit our site for full [T&C's](#)