

18V Cordless Brushless Percussion Drill

R18PDBL-0



BRUSHLESS



- Brushless percussion drill ideal for drilling in wood or metal, driving screws or even drilling in masonry thanks to the hammer function
- Ryobi's Brushless technology uses patented electronics to deliver more runtime and power
- All metal 13mm ratcheting chuck for improved bit gripping strength and durability
- 2 gears to control the max speed to match different materials and applications
- e-Torque control settings make it easy to drive screws flush everytime
- LED lights up your work area for better visibility



Article Number	5133002438
Article Number	5133004690
Battery pack capacity (Ah)	-
Battery type	Li-ion
Charger included?	No
Chuck capacity (mm)	13
EAN Code	4892210135636
EAN Code	4892210184122
Max drilling steel (mm)	13
Max. drilling masonry (mm)	13
Max. drilling wood (mm)	50
Max. percussion rate (bpm)	7040 / 27200
Max. torque (Nm)	60
No load speed (rpm)	0-440 / 0-1700
No. of batteries supplied	0
Power	18V
Sound power level (Lwa)(dB(A))	92.5
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level (Lpa)(dB(A))	81.5
Sound pressure level uncertainty [dB(A)]	3.0
Standard equipment	Double ended bit
Supplied in	Recyclable Carton
Torque settings	10
Vibration drilling into concrete [m/s ²]	9.0
Vibration drilling into concrete uncertainty [m/s ²]	1.5
Vibration drilling into Metal [m/s ²]	1.9
Vibration drilling into metal uncertainty [m/s ²]	1.5
Vibration screw driving [m/s ²]	1.8
Vibration screw driving uncertainty [m/s ²]	1.5
Weight [without battery] [Kg]	1.3

*Registration required for extension from 2-3 years. Please visit our site for full T&C's