

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2162811023](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Cable Assemblies](#)  
**Description:** MX150 Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 600.00mm Length, Tin (Sn) Plating, 2 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)  
[Packaging Specification 2162801021-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">216281</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	MX150-to-Pigtail
Overview	<a href="#">Off-the-Shelf Cable Assemblies</a>
Product Name	MX150
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264714377

**Physical**

Cable Length	600.00mm
Circuits (Loaded)	2
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS/Nylon
Net Weight	378.300/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	3.50mm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size AWG	14
Wire/Cable Type	TXL Stranded


**Electrical**

Current - Maximum per Contact	22.0A
Voltage - Maximum	14V DC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	2162801021-001
Sales Drawing	2162811021-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
D(2020)4578-DC (25  
June 2020)  
di-n-pentyl phthalate  
(DPP)  
perfluorooctanoic acid  
disodium 3,3'-[[1,1'-  
biphenyl]-4,4'-  
diylbis(azo)  
diisopentylphthalate  
1,2-diethoxyethane  
dibutyltin dichloride  
1,3-propanesultone  
ammoniumpentadecafluorooctanoate  
2-ethylhexyl 10-  
ethyl-4,4-dioctyl-7-  
oxo-8-oxa-3,  
2-(2H-benzotriazol-2-  
yl)-4,6-  
ditertpentylphenol  
2-(2H-benzotriazol-2-  
yl)-4-(tert-butyl)-6-  
(sec-b  
1,2-  
Benzenedicarboxylic  
acid, dihexyl ester,  
bra  
diisohexyl phthalate  
1,2-  
benzenedicarboxylic  
acid, dipentylester,  
bra  
n-pentyl-  
isopentylphthalate  
Boric acid  
Nonadecafluorodecanoic  
acid (PFDA) and its  
sodiu

**China RoHS**

Tris(4-nonylphenyl,  
branched and linear)  
phosphi  
Pyrene  
Perfluorononan-1-  
oic acid  
(2,2,3,3,4,4,5,5,6,6,7  
Methylhexahydrophthalic  
anhydride  
reaction mass of  
2-ethylhexyl 10-  
ethyl-4,4-dioct  
Perfluorohexane-1-  
sulphonic acid and its  
salts  
ethylene thiourea  
Lead sulfochromate  
yellow  
strontium chromate  
bis(2-methoxyethyl)  
ether  
pentazinc chromate  
octahydroxide  
1,2-dimethoxyethane  
1,2-bis(2-  
methoxyethoxy)ethane  
bis(pentabromophenyl)  
ether  
cadmium oxide (non-  
pyrophoric)  
cadmium sulphide  
orange lead  
cadmium  
lead dinitrate  
lead oxide sulfate  
pentalead tetraoxide  
sulphate  
dioxobis(stearato)trilead  
Lead titanium  
zirconium oxide  
lead cyanamidate  
Sulfurous acid, lead  
salt, dibasic  
[phthalato(2-)]dioxotrilead  
benzo[a]pyrene  
4-aminoazobenzene  
dihexyl phthalate  
(DnHP)

**Halogen-Free  
Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[216281](#) Series

**Mates With**

[MX150 Sealed Single Row Male Connector  
33481](#)

This document was generated on 10/20/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**