


GEFORCE® GTX 1650 D6 VENTUS XS OCV1



SPECIFICATION

Model Name	GeForce® GTX 1650 D6 VENTUS XS OCV1
Graphics Processing Unit	NVIDIA® GeForce® GTX 1650
Interface	PCI Express x16 3.0
Cores	896 Units
Core Clocks	Boost: 1620 MHz
Memory Speed	12 Gbps
Memory	4GB GDDR6
Memory Bus	128-bit
Output	DL-DVI-D x 1 / HDMI 2.0b x 1 / DisplayPort x 1 (v1.4)
HDCP Support	Y
Power consumption	75 W
Power connectors	6-pin x 1
Recommended PSU	300 W
Card Dimension (mm)	179 x 115 x 42 mm
Weight (Card / Package)	466g / 670g
DirectX Version Support	12 API
OpenGL Version Support	4.6
Maximum Displays	3
G-SYNC® technology	Y
Adaptive Vertical Sync	Y
Digital Maximum Resolution	7680x4320

CONNECTIONS



1. DisplayPort
2. HDMI
3. DVI-D

FEATURE

Afterburner Overclocking Utility

- OC Scanner: An automated function finds the highest stable overclock settings.
- Kombustor: The latest DirectX versions benchmark supporting.
- Predator: In-game video recording.

GeForce Experience

- Capture and share videos, screenshots, and livestreams with friends. Keep your drivers up to date and optimize your game settings.

NVIDIA Ansel

- A powerful photo mode that lets you take professional-grade photographs of your games.