

# GEFORCE® GTX 1650 D6 AERO ITX OCV1



## SPECIFICATION

<b>Model Name</b>	GeForce® GTX 1650 D6 AERO ITX OCV1
<b>Graphics Processing Unit</b>	NVIDIA® GeForce® GTX 1650
<b>Interface</b>	PCI Express x16 3.0
<b>Cores</b>	896 Units
<b>Core Clocks</b>	Boost: 1620 MHz
<b>Memory Speed</b>	12 Gbps
<b>Memory</b>	4GB GDDR6
<b>Memory Bus</b>	128-bit
<b>Output</b>	DL-DVI-D x 1 / DisplayPort x 1 (v1.4) / HDMI 2.0b x 1
<b>HDCP Support</b>	Y
<b>Power consumption</b>	75 W
<b>Power connectors</b>	6 pin x 1
<b>Recommended PSU</b>	300 W
<b>Card Dimension (mm)</b>	171 x 115 x 43 mm
<b>Weight (Card / Package)</b>	449g / 653g
<b>DirectX Version Support</b>	12 API
<b>OpenGL Version Support</b>	4.6
<b>Maximum Displays</b>	3
<b>G-SYNC® technology</b>	Y
<b>Digital Maximum Resolution</b>	7680x4320

## FEATURE

### Afterburner Overclocking Utility

- OC Scanner: An automated function finds the highest stable overclock settings.
- Kombustor: The latest DirectX versions benchmark supporting.
- Predator: In-game video recording.

### GeForce Experience

- Capture and share videos, screenshots, and livestreams with friends. Keep your drivers up to date and optimize your game settings.

### NVIDIA Ansel

- A powerful photo mode that lets you take professional-grade photographs of your games.

## CONNECTIONS



1. DisplayPort
2. HDMI
3. DVI-D