

58495-1 ✓ ACTIVE

AMP

TE Internal #: 58495-1

Portable Crimp Tools, Commercial Crimp Tooling, Operator Releasable & Adjustable, Removable/Interchangeable, TE Product Specification (114-)

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**

Ratchet Configuration: **Operator Releasable & Adjustable**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (114-)**

Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
Certification	Upon Request for Fee
Power Type	Battery, Electric, Manual
Tool Type	PRO-CRIMPER Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)













EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC

Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Model / Part # CAT-AM71-C83998C CMC SERIES 1</p>	 <p>TE Model / Part # CAT-AM71-T98E TYPE III CONTACTS LP</p>	 <p>TE Model / Part # CAT-AM71-T98D TYPE III CONTACTS LP EMEA</p>	 <p>TE Model / Part # CAT-AM71-C83998Y CPC SERIES 1 SEALED ONE-PIECE</p>
 <p>TE Model / Part # CAT-AM71-C83998J CPC SERIES 1</p>	 <p>TE Model / Part # CAT-AM71-C83998K CPC SERIES 6</p>	 <p>TE Model / Part # CAT-AM71-T98C TYPE III CONTACTS STRIP EMEA</p>	 <p>TE Model / Part # CAT-AM71-T98B TYPE III CONTACTS STRIP</p>
 <p>TE Model / Part # 1-66099-2 III+ PIN,18-16,TIN-LEAD,SMPACK</p>	 <p>TE Model / Part # 2-66101-0 III+ SKT,18-16,TIN,SMPACK</p>	 <p>TE Model / Part # 66399-1 III+ SKT,24-20,TIN-LEAD,LP</p>	 <p>TE Model / Part # 66106-3 III+ PIN,26-24,15AU/FL,STRIP</p>



TE Model / Part # 66399-9
III+ SKT,24-20,30AU/FL,SMPACK



TE Model / Part # 66108-6
III+ SKT,26-24,TIN-LEAD,STRIP



TE Model / Part # 1-66107-0
III+ PIN,26-24,30AU/FL,SMPACK



TE Model / Part # 66109-2
III+ SKT,26-24,TIN-LEAD,LP



TE Model / Part # 1-66099-3
III+ PIN,18-16,15AU/FL,SMPACK



TE Model / Part # 66400-1
III+ PIN,24-20,TIN-LEAD,LP



TE Model / Part # 66108-4
III+ SKT,26-24,30AU/FL,STRIP



TE Model / Part # 1-66107-2
III+ PIN,26-24,TIN,SMPACK

Customers Also Bought



TE Model / Part #206708-1
CPC SERIES 6



TE Model / Part #206138-8
CPC CABLE CLAMPS



TE Model / Part #66103-4
TYPE III CONTACTS LP



TE Model / Part #305183
EXTRACT TOOL TYPE 2 20-16

Documents

Datasheets & Catalog Pages

[1-1773865-2_1015_Commercial Manual Hand Tools](#)

English

Signal Contacts

English

[AMP Circular Connectors for Commercial Signal & Power Applications](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

Bottoming Dies

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)



English

[PRO-CRIMPER II Hand Application Tool 58495-1 w/Die Assembly 58495-2](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[Agency Approvals](#)

[CSA Certificate](#)

English