

08003

# DEWALT®

## DXV20S PROFESSIONAL WET & DRY VACUUM CLEANER

**Stainless Steel quality casing with hard wearing castors**  
**Durable side catches & large sturdy On/OFF switch**  
**Automatic ball-cock air shut-off**  
**Blower feature for removing dust & debris**  
**Lightweight & portable**  
**Powerful suction/blower motor**  
**Hose & accessories supplied**

**20**  
LITRE

**1050**  
W

**48 MM**  
HOSE  
DIAMETER



# DXV20S PROFESSIONAL WET & DRY VACUUM CLEANER

## SPECIFICATIONS:

Input Supply	230 v 13 A
Power	1050 Watts
Mains Lead	3 m
Pressure	15 kPa (0,15 bar)
Air Flow	37,8 L/s
Tank Capacity	20 Litres
Hose	2,1 m x 48 mm
Net Weight	5,5 kG
Gross Weight	8,2 kG
Pack Dimensions	395 x 380 x 475 mm
Warranty	3 Year Limited

## ACCESSORIES INCLUDED:



**DXVC4001  
CARTRIDGE FILTER**



**DXVA19-1400  
CREVICE NOZZLE**



**DXVA19-1900D  
FLOOR NOZZLE**



**DXVA19-1300  
UTILITY NOZZLE**



**DXVA25-4204  
DISPOSABLE DUST BAG**



**DXVA19-1202  
EXTENSION WAND**



**DXVA19-2558  
HOSE**



**DXVA19-5158  
HOLDER/BAG**

**GUARANTEED TOUGH®**

Online Customer Service Centre at: [www.2helpU.com](http://www.2helpU.com)

**DEWALT®**