

08005

# DEWALT®

## DXAM2250 CENTRIFUGAL AIR MOVER

**3 Speed Settings - Low/Medium/High**

**3 Blowing Positions - Horizontal / 45° / 90°**

**Versatile for drying wet floors, shampooed carpets,  
plastered walls & ceilings etc.**

**Easy Positioning - Direct the airflow where it is needed**

**Portable with ergonomic handle & front safety grill**

**150  
W**

**236  
LTR/S**

**500  
CFM**

**AIR LOW**



# DXAM2250 CENTRIFUGAL AIR MOVER

## SPECIFICATIONS:

Input Supply	230 v 13 A
Power	1,5 HP (150 Watts)
Mains Lead	3 m
Air Flow	236 L/s (500 CFM)
Warranty	3 Year Limited

**GUARANTEED TOUGH®**

Online Customer Service Centre at: [www.2helpU.com](http://www.2helpU.com)

**DEWALT®**