

Tab M10 FHD Plus with the Smart Charging Station ZA5W0163GB

Product

Lenovo TB-X606F

Region

UKI

Country/Region

United Kingdom

Machine Type

ZA5W

TopSeller

No

Processor

MediaTek Helio P22T (8C, 8x A53 @2.3GHz)

Graphics

Integrated IMG GE8320 GPU

Chipset

MediaTek SoC Platform

Memory

2GB Soldered LPDDR4X-3200

Display

10.3" FHD (1920x1200) TDDI 330nits

Touchscreen

10-point Multi-touch

Expandable Memory

MicroSD card (Up to 256GB)

Storage

32GB eMMC

WLAN + Bluetooth

11a/b/g/n/ac, 1x1 + BT5.0

WWAN

None

Card Slot

MicroSD Card Holder Tray

Bundled Accessories

Smart Charging Station (Cradle)

Color

Iron Grey

Case Material

Metal

Camera

Front 5.0MP / Rear 8.0MP

Microphone

2x, Array

VoiceCall

No

Battery

Integrated 5000mAh

Power Adapter

5V / 2.0A

Operating System

Android Pie

Base Warranty

1-year, Depot

EAN / UPC / JAN

194632277234

Announce Date

2020-01-28

Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Tab M10 FHD Plus with the Smart Charging Station Platform Specifications

Product Specifications Reference (PSREF)



Processor	MediaTek® Processor MediaTek Helio P22T (8xARM Cortex-A53, up to 2.3GHz)						Camera	Front / Focus Mode		Rear / Focus Mode		Type	Zoom	Flash Light	
Graphics	Integrated IMG GE8320 GPU							5.0MP	Fixed Focus	8.0MP	Auto Focus	CMOS	Digital	No	
Display	Size	Resolution	Type	Brightness		Color Gamut	Viewing Angle								
	10.3" (261.62mm)	FHD (1920 x 1200)	TDDI	Typ. 330nits Min. 280nits	Typ. 70.3% NTSC Min. 65% NTSC	160°									
Multi-touch	Capacitive-type multi-touch, supports 10-point touch						Audio	Dual side speaker, tuned with Dolby Atmos® Dual array microphones (with dedicated DSP), 3.5mm (0.14inch) combo audio / microphone jack (CTIA)							
Memory	2GB or 4GB / 3200MHz LPDDR4X, soldered to systemboard						Keyboard	None							
Storage	32GB, 64GB or 128GB eMMC (Embedded Multi Media Card), flash memory on board						Touchpad	None							
Card slot	One single card slot (WiFi model) or one dual-card slot (LTE model), supports Nano-SIM card + MicroSD card (up to 256GB, FAT32)						Bundled Accy	Cradle: Smart Charging Station with Micro-USB cable							
Bluetooth®	Bluetooth 5.0						Security chip	None							
WLAN	802.11 a/b/g/n/ac, 1x1, 2.4 GHz / 5 GHz Wi-Fi Dual Bands						Fingerprint reader	None							
WWAN (Optional)	4G LTE connectivity						VoiceCall	None							
LTE Band	GSM: B2/B3/B5/B8 WCDMA: B1/B2/B5(B6/B19)/B8 FDD LTE: B1/B2/B3(expanded Band3)/B4/B5(B19)/B7/B8/B20 TDD LTE: B38/B40						Battery type	Li-ion Polymer 5000mAh (Minimum) / 5100mAh (Typical)							
NFC	None						Battery life	Standby Time: 1048hrs Online Video playback Time: Up to 8.5hrs Browsing Time: Up to 9hrs <i>* Battery life varies significantly with hardware configurations, settings, usage, & other factors</i>							
WIFI Direct	Yes						AC adapter	5V/2A (USB Type-C™)							
WIFI Display	Yes						Charging time	Over 3.5hrs							
WHDI	None						Preload	Android® Pie Lenovo applications • Tips • Kid's Mode				Third-party applications • Netflix • Dolby Atmos • Google • Gmail • Google Chrome • Google Photos • Google Play Store			
FM Radio	Yes						<i>*Applications vary from different Android Pie versions</i>								
A-GPS (Optional)	Yes (LTE model)						Limited warranty	<i>One of the following, configurable by model:</i> • 1-year courier / depot service • 1-year customer carry-in service • 2-year/1-yr battery mail-in service • 2-year/1-yr battery courier / depot service							
GPS (Optional)	Yes (LTE model)						Environment	RoHS-compliant							
Glonass (Opt)	Yes (LTE model)														
Beidou (Optional)	Yes (LTE model)														
Vibrator	Yes														
G-sensor	Accelerometer sensor														
P-sensor	Proximity sensor														
L-sensor	Ambient sensor														
E-compass	None														
Hall Sensor	Yes														
Gyroscope	None														
Proofing	None														
Dimensions	Tablet: 9.61" x 6.03" x 0.32"; 244.2mm x 153.3mm x 8.15mm Cradle: 4.92" x 3.62" x 0.66"; 125mm x 92mm x 17mm														
Weight	Tablet: 460g / 1.01lb Cradle: 245g / 0.54lb														
Case color	Iron Grey														
Case material	Metal														
Ports	Two Pogo Pin, one USB Type-C 2.0, supports OTG, 3.5mm (0.14inch) combo audio / microphone jack (CTIA), One single card slot (WiFi model) or one dual-card slot (LTE model), supports Nano-SIM card + MicroSD card (up to 256GB, FAT32) <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>														
Buttons	Power key, volume key														

The specifications above may not be available in all regions and might change by region.

Lenovo
July 2020

Tab M10 FHD Plus with the Smart Charging Station

