

ThinkBook 14 IML 20RV00AUUK

Product

ThinkBook 14 IML

Region

WE

Country/Region

UK Group

Machine Type

20RV

TopSeller

TopSeller

Processor

Intel Core i5-10210U (4C / 8T, 1.6 / 4.2GHz, 6MB)

Graphics

Integrated Intel UHD Graphics

Chipset

Intel SoC Platform

Memory

8GB Soldered DDR4-2666

Storage

256GB SSD M.2 2280 PCIe NVMe

Optane Memory

None

Display

14" FHD (1920x1080) IPS 250nits Anti-glare

Touchscreen

None

Optical

None

Media Reader

4-in-1 Card Reader

Ethernet

100/1000M

WLAN + Bluetooth

11ax, 2x2 + BT5.0

Case Material

Aluminium

Camera

720p with ThinkShutter

Microphone

2x, Array

Color

Mineral Grey

Surface Treatment

Anodizing sandblasting

Keyboard

Backlit, English (UK)

Fingerprint Reader

Touch Style

TPM

FW TPM 2.0

Battery

Integrated 45Wh

Power Adapter

65W Slim Tip

Operating System

Windows 10 Home 64, English

Bundled Software

Office Trial

Base Warranty

1-year, Depot

Bundled Service

None

EAN / UPC / JAN

194632152869

End of Support

2026-05-14

Announce Date

2019-10-15

 WWW.LENVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

ThinkBook 14 IML Platform Specifications

Product Specifications Reference (PSREF)

Processor	10th Generation Intel® Core™ i3 / i5 / i7 Processor							Media reader Ports	4-in-1 media reader (MMC, SD, SDHC, SDXC) One hidden USB 2.0, two USB 3.1 Gen 1 (one with Always On), One USB-C 3.1 Gen 1, one USB-C 3.1 Gen 2 (with the function of DisplayPort and power delivery), 4-in-1 media reader (MMC, SD, SDHC, SDXC), Ethernet (RJ45), HDMI 1.4b, headphone / microphone combo jack, AC power adapter jack <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>		
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types			DDR4-2666	Processor Graphics
	i3-10110U	2	4	2.1 GHz	4.1 GHz	4MB	Intel UHD Graphics				
	i5-10210U	4	8	1.6 GHz	4.2 GHz	6MB					
	i7-10510U			1.8 GHz	4.9 GHz	8MB					
i7-10710U	6	12	1.1 GHz	4.7 GHz	12MB						
Graphics	Intel UHD Graphics in processor only or, Intel UHD Graphics in processor and AMD Radeon™ 625, 2GB GDDR5 memory; supports external digital monitor via HDMI or USB Type-C; supports three independent displays; Max resolution: 3840x2160@60Hz (USB Type-C); 3840x2160@30Hz (HDMI)							Camera Audio support	HD720p, fixed focus, ThinkShutter, integrated dual array digital microphone HD Audio, Realtek ALC3287 codec, stereo speakers, 2W x 2, Dolby Audio™, dual array digital microphone		
Chipset	Intel SoC (System on Chip) platform							Keyboard Trackpad	6-row, spill-resistant, multimedia Fn keys, optional LED backlight Buttonless Mylar surface touchpad, multi-touch		
Memory	Supports up to 40GB / 2666MHz DDR4, 4GB or 8GB memory soldered to systemboard, one DDR4 SO-DIMM socket							Security Security chip	Power-on password, hard disk password, supervisor password Firmware TPM 2.0 integrated in chipset		
Display	Size	Resolution	Surface	Type	Brightness	Aspect Ratio	Contrast Ratio	Fingerprint reader	<i>Optional:</i> Touch style fingerprint reader on power button		
	14.0" (356mm)	FHD (1920x1080)	Anti-glare	TN	220 nits	16:9	500:1	Battery	Integrated Li-Polymer 45Wh (supports Rapid Charge 1 hr 80%) or 57Wh battery		
	14.0" (356mm)	FHD (1920x1080)	Anti-glare	WVA	250 nits	16:9	800:1	Max battery life	<i>MobileMark® 2014:</i> 9 hr (45Wh) or 12 hr (57Wh) <i>* Battery life varies significantly with hardware configurations, settings, usage, & other factors</i>		
Multi-touch	None							AC adapter	65W slim tip (rectangle) or slim USB-C AC adapter		
Storage	Up to 2 drives (one HDD and one M.2 SSD): • HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high, Active Protection System • M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 2 • M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4 • Intel Optane™ Memory H10 with SSD, M.2 2280, PCIe NVMe 3.0 x 4							Preload (optional)	<i>Preloaded operating system</i> • Windows® 10 Home 64 • Windows 10 Home in S mode • Windows 10 Pro 64 • Windows 10 Pro in S mode <i>Preloaded applications (only some listed)</i> • Microsoft Office Home and Business 2019 • Microsoft Office Home and Student 2019 • Microsoft Office Professional 2019 • Microsoft Office Trial (with 30-day license) • Microsoft Office 365 Personal • Microsoft Office 365 Home • Microsoft Office Personal 2019		
Optane Memory	Optional 16GB Intel Optane Memory PCIe NVMe, PCIe 3.0 x 2, 16Gb/s, M.2							Limited warranty	<i>One of the following, configurable by model:</i> • 1-year depot repair service • 1-year depot with 2-year system board repair service • 2-year/1-yr battery depot repair service		
Optical	None							Mil-Spec test	MIL-STD-810G military testing		
Ethernet	Gigabit Ethernet connection							Environment	EPEAT™ Silver; ENERGY STAR® 8.0; ErP lot3, RoHS-compliant		
WLAN + Bluetooth™	<i>One of the following, configurable by model:</i> • 802.11ac 1x1 Wi-Fi + Bluetooth 5.0, M.2 card • 802.11ac 2x2 Wi-Fi + Bluetooth 5.0, M.2 card • 802.11ax 2x2 Wi-Fi + Bluetooth 5.0, M.2 card										
Dimensions	WxDxH: 12.8" x 9.06" x 0.7"; 326mm x 230mm x 17.9mm										
Weight	Starting at 3.3 lb / 1.5 kg										
Case color	Mineral Grey										
Case material	Aluminum										

The specifications above may not be available in all regions and might change by regions

Lenovo
October 2020



ThinkBook 14 IML

