

# Gigaset A170

## Pure communication

- Illuminated graphical display
- Long talk and standby time of up to 18 and 200 hours
- Telephone book for up to 50 entries
- Easy to operate keypad



## Audio quality

- Adjustable volume of handset sound (5 levels)
- Ringer melody output via earpiece
- Advisory tone for key confirmation and low battery
- Echo-mode for a better acoustic performance behind a router
- Hearing-aid-compatible

## Telephone book and dialling functions

- Telephone book for up to 50 names and numbers
- Call preparation (input of the number before the actual dialling procedure) with correction option
- Redial of the last 10 different numbers
- Programmable shortcut keys (keys 2 – 9)
- Dialling procedure: Dual-tone multi-frequency dialling (DTMF), pulse dialling (DP)
- Dialling key (programmable flash times)

## Display

- Illuminated graphic-display, 1.5", 34 x 22 mm, 1-line dot matrix with 14 characters + 1 line for icons + 1 line for soft keys
- Display illumination: amber
- In standby mode:
  - Display of date and time
  - Display of battery charge status
  - Soft keys for quick selection of functions

- Alarm clock symbol if alarm time is set
- Number of registered handsets
- During a call: display of call duration

## Call display and signalling

- Call display with telephone number or name (CLIP / CNIP)
- For incoming and missed calls
- Adjustable ringtones
  - 10 melodies in the handset
  - 5 volume levels + OFF + crescendo
- Individual ringtones for internal / external calls

## Display of missed calls / caller list

- Missed calls are shown in the display
- List of the last 25 calls with telephone number / name and time
- Direct dialling out of missed caller list via send button

## Keypad

- 12 numeric keys plus 5 function keys
- 2-way-navi-key
- Key lock on/off via pound (#) key
- Ringtone on/off via asterisk (\*) key
- Flash function (R) through long press on "0"-key

## Menu

- Convenient menu guidance in various languages (D, GB, F, I, E, P, TR, etc.)
- Simple operation via text-based menus and soft keys

# Gigaset

Wherever you go.

## Additional functions

- Plug-and-play - very easy installation: unpack, plug in, and call (handset registered ex works)
- Alarm clock feature with adjustable melody
- Date and time functions, telephone book, caller lists and settings are saved in the event of a power failure

## Features when operating multiple handsets

- Toll-free internal calling
- 2 calls possible at the same time (1 external and 1 internal between 2 handsets)
- Telephone book transfer between handsets
- Internal call to all or selected handsets
- Call forwarding to a different handset with dialling/call-back function
- 3-way-conference (1 external and 2 internal parties)
- Simultaneous ringing of all handsets for external calls

## ECO DECT

- Automatic reduction of the transmitting power depending on the distance between the handset and the base station
- Radiation-free in standby mode, even if several handsets are used, as long as all registered handsets support ECO DECT

## Technical data

Configuration	<ul style="list-style-type: none"> <li>○ Connection of 1 external line (a/b)</li> <li>○ Limited expandability for more information also see <a href="http://www.gigaset.com/compatibility">www.gigaset.com/compatibility</a></li> </ul>
Interface	a/b (analogue)
Implementation	Main connection (PSTN) / telecommunications system (PBX)
Standards	DECT
Handset	<ul style="list-style-type: none"> <li>○ Standby: up to 200 hours</li> <li>○ Talk time: up to 18 hours</li> <li>○ Batteries: 2 x AAA (NiMH), rechargeable</li> <li>○ Range <ul style="list-style-type: none"> <li>- in buildings: up to 50 m</li> <li>- outdoors: up to 300 m</li> </ul> </li> <li>○ Dimensions: 159 x 48 x 30 mm (H x W x D)</li> <li>○ Weight: 108 g (incl. batteries)</li> </ul>
Base station	<ul style="list-style-type: none"> <li>○ Power supply: 230 V plug in power adaptor</li> <li>○ Dimensions: 89 x 89 x 43 mm (H x W x D)</li> <li>○ Weight: 63 g</li> </ul>
Charger (for duos/trios only)	<ul style="list-style-type: none"> <li>○ Power supply: 230 V plug-in power adaptor</li> <li>○ Dimensions: 75 x 69 x 38 mm (H x W x D)</li> <li>○ Weight: 34 g</li> <li>○ Charger suited for wall mounting</li> </ul>
Scope of supply	<ul style="list-style-type: none"> <li>○ 1 Base station Gigaset A170</li> <li>○ 1 Handset Gigaset A170H</li> <li>○ 1 Plug in power adaptor</li> <li>○ 1 Telephone connection cable</li> <li>○ 2 AAA rechargeable batteries (NiMH)</li> <li>○ 1 Battery compartment cover</li> <li>○ 1 User manual</li> </ul>
Appliance colour	<ul style="list-style-type: none"> <li>○ Black</li> <li>○ White</li> </ul>
Datasheet-Version	04.09.2017