

NEBO[®] SWYVEL



Your next Go-To flashlight has arrived. Compact, 1000 lumens, rechargeable, and a 90° rotating head. And that's not all.

The SWYVEL is a versatile, **rechargeable** flashlight that features **Smart Power Control**, which smoothly transitions the 5 light modes, including the **1,000 lumen Turbo Mode**. The compact size and steel clip provide convenient carry, and the 90° swivel head and magnetic base give you hands-free light in any direction. The SWYVEL is small enough for your pocket and bright enough for any job.

5 LIGHT MODES

- High (500 lumens) - 1 hour / 100 meters
- Medium (200 lumens) - 1.75 hours / 60 meters
- Low (50 lumens) - 6 hours / 30 meters
- Strobe (500 lumens) - 1 hours / 100 meters
- TURBO (1000 lumens) - 30 seconds / 130 meters

DESIGN

- USB Rechargeable
- Anodized aircraft-grade aluminum; water (IPX4) and impact-resistant
- 90° swivel head
- Smart Power Control
- Removable steel belt/pocket clip
- Battery charging indicator

OPERATION

- Top-positioned ON/OFF button

ACCESSORIES

- MagDock USB charging cable included

BATTERIES

- Powered by rechargeable battery (included)
(Recharge time: 4 hours)

SPECS

- 0.18 lbs.
- (H) 3.75" x (W) 1" x (D) 1.125"



Actual Size



- Each SWYVEL comes in a gift box.

Display Dimensions

(H) 5.31" x (W) 5.67" x (D) 7.87"

Gift Box Dimensions

(H) 3.78" x (W) 2.36" x (D) 2.5"

Attractive SWYVEL Counter Display sold separately (Tethered Try Me sample included).



UPC CODE

ITEM

DESCRIPTION

645397935612

6907

SWYVEL

645397935766

6907DISPLAY

SWYVEL Display with Try Me Sample