

Hot-melt glue applicator

Gluematic 3002

Folding box

EAN 4007841 333317



Ø11mm

Glue sticks



CE



VDE

Function description

One for almost all. Hot-glue melt applicator Gluematic 3002, for hobby and trade use, high delivery rate of 16 g/min, small and practical, heating-up time of just 7 minutes, interchangeable nozzles.

Technical specifications

Output, heat-up phase	200 W
Average power consumption	45 W
Temperature	206 °C
Melt temperature	206 °C
Warm-up time	7 min
Delivery rate	16 gr/min
Max. stick diameter	11 mm
Function, hanger	No
Soft grip	No

Stroke adjustment	No
Idle mode	No
Dimensions (L x W x H)	185 x 30 x 160 mm
Nozzle can be changed	Yes
Mains power supply	100 – 240 V / 50 – 60 Hz
Suitable for	Glass, Rubber, Wood, ceramic, Leather, Paper, Card / cardboard boxes, PP, Textiles
PU1, net weight	0,317 kg
Manufacturer's Warranty	3 years
PU1, EAN	4007841333317

Hot-melt glue applicator

Gluematic 3002

Folding box

EAN 4007841 333317



Accessories

EAN 4007841 076061	Standard 2 mm nozzle for Gluematic 3002 / 5000
EAN 4007841 075965	Long nozzle 2.8 mm for Gluematic 3002 / 5000
EAN 4007841 076160	Fine nozzle 1.0 mm for Gluematic 3002 / 5000
EAN 4007841 048419	Glue sticks Ø 11 mm Crystal
EAN 4007841 044930	Glue sticks, Ø 11 mm Ultra-Power
EAN 4007841 046910	Glue sticks, Ø 11 mm Ultra-Power
EAN 4007841 006808	Glue sticks Ø 11 mm white
EAN 4007841 006815	Color sticks Ø 11 mm
EAN 4007841 006822	Glue sticks Ø 11 mm Crystal
EAN 4007841 006778	Glue sticks Ø 11 mm wood
EAN 4007841 006761	Glue sticks, Ø 11 mm Ultra-Power
EAN 4007841 006792	Glue sticks Ø 11 mm black
EAN 4007841 006754	Glue sticks Ø 11 mm Crystal