



**Brother, MFC-J895DW A4 Colour
Inkjet MFP
DATA SHEET**



Product Information

Brand	Brother
SKU	10182209
Manu Part #	MFCJ895DWZU1

Features

Feature 1	Print, copy, scan & fax
Feature 2	Automatic 2-sided print
Feature 3	Easy to use 6.8cm touchscreen

Weight & dimensions

Weight	6.6 kg
Width	400 mm
Depth	341 mm
Height	172 mm

Design

Product colour	Black,White
Market positioning	Home & Office
Built-in display	Y
Display	LCD
Display diagonal	6.86 cm (2.7)
Touchscreen	Y
Control type	Touch
Colour display	Y

Packaging data

Package weight	9.8 kg
Package width	477 mm
Package height	457 mm
Package depth	294 mm

Network

Ethernet LAN	Y
Wi-Fi	Y

Wi-Fi standards	802.11b,802.11g,Wi-Fi 4 (802.11n)
Ethernet LAN data rates	10,100 Mbit/s
Cabling technology	10/100Base-T(X)
Security algorithms	64-bit WEP,128-bit WEP,WPA-AES,WPA-PSK,WPA-TKIP, WPA2-AES,WPA2-PSK
Near Field Communication (NFC)	Y
Mobile printing technologies Apple AirPrint, Brother iPrint & Scan, Google Cloud Print, Mopria Print Service	Apple AirPrint, Brother iPrint & Scan, Google Cloud Print, Mopria Print Service
Supported network protocols (IPv4)	ARP, RARP, BOOTP, DHCP, APIPA(Auto IP), WINS/NetBIOS name resolution, DNS Resolver, mDNS, LLMNR responder, LPR/LPD, Custom Raw Port/Port9100, SNMPv1/v2c, TFTP server, ICMP, Web Services (Print/Scan), SNTTP Client
Supported network protocols (IPv6)	NDP, RA, mDNS, LLMNR Responder, DNS Resolver, LPR/LPD, Custom Raw Port/Port9100, SNMPv1/v2c, TFTP server, Web Services (Print/Scan), SNTTP Client, ICMPv6

Packaging content

Cables included	Phone
Manual	Y
Quick installation guide	Y
Power cord included	Y
Warranty card	Y
Drivers included	Y
Cartridge(s) included	Y

System requirements

Windows operating systems supported	Windows 7,Windows 7 Enterprise,Windows 7 Enterprise x64,Windows 7 Home Basic,Windows 7 Home Basic x64,Windows 7 Home Premium,Windows 7 Home Premium x64,Windows 7 Professional,Windows 7 Professional x64,Windows 7 Starter,Windows 7 Starter x64,Windows 7 Ultimate,Windows 7 Ultimate x64,Windows 7 x64,Windows 8,Windows 8 Enterprise,Windows 8 Enterprise x64,Windows 8 Pro,Windows 8 Pro x64,Windows 8 x64,Windows 8.1,Windows 8.1 Enterprise,Windows 8.1 Enterprise x64,Windows 8.1 Pro,Windows 8.1 Pro x64,Windows 8.1 x64,Windows Vista,Windows Vista Business,Windows Vista Business x64,Windows Vista Enterprise,Windows Vista Enterprise x64,Windows Vista Home Basic,Windows Vista Home Basic x64,Windows Vista Home Premium,Windows Vista Home Premium x64,Windows Vista Ultimate,Windows Vista Ultimate x64,Windows Vista x64,Windows XP Home,Windows XP Home x64,Windows XP Professional,Windows XP Professional x64
Mac operating systems supported	Mac OS X 10.10 Yosemite,Mac OS X 10.8 Mountain Lion,Mac OS X 10.9 Mavericks

General

Printing colours	Black, Cyan, Magenta, yellow
Number of print cartridges	4

Ports & interfaces

USB port	Y
Standard interfaces	Ethernet,NFC,USB 2.0,Wireless LAN
Direct printing	Y

Power

Power consumption (off)	0.2 W
Energy Star certified	Y
Power consumption (sleep)	1.2 W
Power consumption (ready)	3.5 W
Power consumption (average operating)	17 W

Performance

Internal memory	128 MB
Card reader integrated	Y
Sound pressure level (printing)	50 dB
Compatible memory cards	MMC,SD,SDHC,SDXC

Printing

Maximum resolution	6000 x 1200 DPI
Print technology	Inkjet
Duplex printing	Y
Printing	Color printing
Duplex printing mode	Auto
Print speed (ISO/IEC 24734) mono	12 ipm

Print speed (ISO/IEC 24734) colour	10 ipm
------------------------------------	--------

Paper handling

Maximum ISO A-series paper size	A4
Paper tray media types	Envelopes,Photo paper,Plain paper
Envelopes sizes	C5,Com-10,DL,Monarch
Paper tray media weight	64 - 220 g/m ²
Multi-purpose tray media types	Envelopes,Executive,Glossy paper,Letter,Plain paper, Recycled paper
Photo paper sizes	10x15 cm

Input & output capacity

Total input capacity	150 sheets
Total output capacity	50 sheets
Paper input type	Paper tray
Multi-Purpose tray input capacity	20 sheets
Multi-Purpose tray	Y
Auto document feeder (ADF) input capacity	20 sheets
Auto document feeder (ADF)	Y
Total number of input trays	1

Scanning

Optical scanning resolution	1200 x 2400 DPI
Scanning	Color scanning
Scan to	Cloud,E-mail,Image,Memory Card,OCR,USB
Scanner type	Flatbed & ADF
Image formats supported	BMP,JPG,PNG,TIFF
Document formats supported	PDF
Output colour depth	24 bit
Input colour depth	30 bit
Maximum scan resolution	19200 x 19200 DPI
Scan drivers	ICA,SANE,TWAIN,WIA

Copying

Copying	Color copying
Copier resize	25 - 400%
Maximum copy resolution	1200 x 1200 DPI
Maximum number of copies	99 copies
N-in-1 copy function	Y

Fax

Modem speed	14.4 Kbit/s
Faxing	Mono faxing
Fax memory	200 pages
Fax forwarding	Y
Fax delayed sending	Y

Certificates

Blue Angel certified	Y
Nordic Swan certified	Y

Other features

Software CD	Y
-------------	---

Product Description

All-in-one Wireless Inkjet Printer + NFC
Space saving A4 inkjet with touchscreen, 2-sided print and automatic document feeder (ADF).
The cleverly compact, cost effective MFC-J895DW is an easy to use 4-in-1 A4 inkjet printer. Ideal for any home or small office, the user friendly MFC-J895DW combines print, scan, copy and fax functionality with a sleek stylish design that fits in those small spaces, whilst maintaining its high-quality printing and reliability. Its simple touchscreen and mobile connectivity makes it easier than ever to complete jobs.
Everything you need: Print, copy, scan & fax
Vivid inkjet colour printing plus accurate copying, high resolution scanning and the added flexibility of fax come together in one stylish package to make the MFC-J895DW a truly diverse machine for all your home or small office needs. So if you're looking for a machine that does it all, meet the Brother MFC-J895DW.
A range of connectivity options for the entire house
Cleverly compact, the MFC-J895DW brings affordable, high-quality printing to your home. With a range of connectivity options to suit, connecting from multiple devices is quick and easy and you don't even have to be in the same room either thanks to wireless printing.
Easy to use with minimal intervention
The MFC-J895DW comes with an intuitive 6.8cm colour touchscreen for easy user control and a 20 sheet Automatic Document Feeder that allows you to scan and copy multi-page documents - perfect for multi-tasking!
Save time with direct photo printing from USB
To print off pictures stored on USB flash memory drives, previously you may have to turn on a computer, connect it and then print from your computer. With the Brother MFC-J895DW, it's much easier. Simply put the USB directly into the printer and select the images you want to print from the touchscreen.

